

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584782

Luminaire Tested: **HC850D010-HM82555827-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555827-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5151.3 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584782

CATALOG NUMBER: HC850D010-HM82555827-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584782

CATALOG NUMBER: HC850D010-HM82555827-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	969552
5°	621893
10°	280931
15°	169507
20°	129171
25°	104311
30°	76440
35°	27676
40°	10329
45°	4688
50°	1497
55°	371
60°	216
65°	255
70°	0
75°	0
80°	622
85°	1238



TEST NUMBER: P584782

CATALOG NUMBER: HC850D010-HM82555827-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1532.3	29.7
10°-20°	1556.4	30.2
20°-30°	1393.2	27.0
30°-40°	561.2	10.9
40°-50°	92.0	1.8
50°-60°	8.4	0.2
60°-70°	3.0	0.1
70°-80°	2.3	0.0
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4481.9	87.0
0°-40°	5043.1	97.9
0°-60°	5143.5	99.8
0°-90°	5152.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5151.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31442	
5°	20091	###
15°	5310	1556
25°	3066	1393
35°	735	561
45°	108	92
55°	7	8
65°	4	3
75°	0	2
85°	4	3
90°	0	



TEST NUMBER: P584782

CATALOG NUMBER: HC850D010-HM82555827-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	31441.9
0.5°	31344.7
1°	30939.0
1.5°	30286.9
2°	29298.5
2.5°	28129.8
3°	26666.3
3.5°	25060.6
4°	23472.1
4.5°	21693.0
5°	20090.8
5.5°	18346.3
6°	16931.3
6.5°	15457.3
7°	14299.0
7.5°	13074.8
8°	12089.8
8.5°	11101.4
9°	10359.2
9.5°	9540.8
10°	8972.0
12.5°	6617.1
15°	5309.7
17.5°	4536.3
20°	3936.3
22.5°	3457.7
25°	3065.8
27.5°	2673.9
30°	2146.8
32.5°	1380.4
35°	735.2
37.5°	405.8
40°	256.6
42.5°	170.0
45°	107.5
47.5°	65.9
50°	31.2
52.5°	10.4
55°	6.9
57.5°	3.5
60°	3.5
62.5°	3.5
65°	3.5



TEST NUMBER: P584782

CATALOG NUMBER: HC850D010-HM82555827-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	3.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.5
70°		0.0



(END OF REPORT)