

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584785

Luminaire Tested: **HC850D010-HM82555827-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555827-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5158.1 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584785

CATALOG NUMBER: HC850D010-HM82555827-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584785

CATALOG NUMBER: HC850D010-HM82555827-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89				89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79				79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64				64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53				53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49				49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45				45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42				42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39				39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121076
5°	119498
10°	115125
15°	110620
20°	107562
25°	104325
30°	93617
35°	61371
40°	33926
45°	28289
50°	25790
55°	24617
60°	22893
65°	20751
70°	18762
75°	16954
80°	15396
85°	14718



TEST NUMBER: P584785

CATALOG NUMBER: HC850D010-HM82555827-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	362.7	7.0
10°-20°	977.6	19.0
20°-30°	1391.3	27.0
30°-40°	1029.7	20.0
40°-50°	510.0	9.9
50°-60°	407.1	7.9
60°-70°	282.6	5.5
70°-80°	152.3	3.0
80°-90°	44.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2731.6	53.0
0°-40°	3761.4	72.9
0°-60°	4678.4	90.7
0°-90°	5158.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5158.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3926	
5°	3860	363
15°	3465	978
25°	3066	1391
35°	1630	1030
45°	649	510
55°	458	407
65°	284	283
75°	142	152
85°	42	45
90°	0	



TEST NUMBER: P584785

CATALOG NUMBER: HC850D010-HM82555827-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3926.4
2.5°	3909.1
5°	3860.5
7.5°	3784.2
10°	3676.7
12.5°	3565.7
15°	3465.1
17.5°	3368.0
20°	3277.8
22.5°	3187.6
25°	3066.2
27.5°	2889.3
30°	2629.2
32.5°	2230.3
35°	1630.3
37.5°	1113.4
40°	842.8
42.5°	721.5
45°	648.7
47.5°	589.6
50°	537.6
52.5°	492.5
55°	457.9
57.5°	416.3
60°	371.2
62.5°	326.0
65°	284.4
67.5°	242.8
70°	208.1
72.5°	173.5
75°	142.3
77.5°	114.4
80°	86.7
82.5°	62.4
85°	41.6
87.5°	17.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)