

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584808

Luminaire Tested: **HC850D010-HM82555830-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555830-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5202.9 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584808

CATALOG NUMBER: HC850D010-HM82555830-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584808

CATALOG NUMBER: HC850D010-HM82555830-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104020
5°	103891
10°	102863
15°	101630
20°	100691
25°	99558
30°	93941
35°	76497
40°	42263
45°	28211
50°	25023
55°	23488
60°	23189
65°	22977
70°	20764
75°	18562
80°	16231
85°	14400



TEST NUMBER: P584808

CATALOG NUMBER: HC850D010-HM82555830-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.1	6.1
10°-20°	898.9	17.3
20°-30°	1335.7	25.7
30°-40°	1202.9	23.1
40°-50°	533.2	10.2
50°-60°	394.9	7.6
60°-70°	307.1	5.9
70°-80°	166.5	3.2
80°-90°	45.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2552.7	49.1
0°-40°	3755.5	72.2
0°-60°	4683.7	90.0
0°-90°	5202.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5202.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3373	
5°	3356	318
15°	3184	899
25°	2926	1336
35°	2032	1203
45°	647	533
55°	437	395
65°	315	307
75°	156	166
85°	41	46
90°	0	



TEST NUMBER: P584808

CATALOG NUMBER: HC850D010-HM82555830-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3373.3
2.5°	3366.5
5°	3356.3
7.5°	3329.2
10°	3285.1
12.5°	3234.4
15°	3183.5
17.5°	3132.8
20°	3068.4
22.5°	3004.1
25°	2926.1
27.5°	2807.6
30°	2638.3
32.5°	2394.5
35°	2032.1
37.5°	1517.2
40°	1049.9
42.5°	775.5
45°	646.9
47.5°	572.3
50°	521.6
52.5°	474.1
55°	436.9
57.5°	406.5
60°	376.0
62.5°	348.8
65°	314.9
67.5°	274.4
70°	230.3
72.5°	193.0
75°	155.8
77.5°	121.9
80°	91.4
82.5°	64.3
85°	40.7
87.5°	17.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)