

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584822

Luminaire Tested: **HC850D010-HM82555835-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555835-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5378.7 lumens
Efficiency: N/A
Efficacy: 112.1 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584822

CATALOG NUMBER: HC850D010-HM82555835-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584822

CATALOG NUMBER: HC850D010-HM82555835-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 93 | 92 | | | |
| 2 | 106 | 100 | 95 | 92 | 104 | 98 | 94 | 91 | 95 | 92 | 89 | 92 | 89 | 87 | 89 | 87 | 85 | 83 | | | |
| 3 | 99 | 92 | 86 | 81 | 97 | 90 | 85 | 81 | 88 | 83 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 75 | | | |
| 4 | 93 | 84 | 78 | 73 | 91 | 83 | 77 | 72 | 81 | 76 | 71 | 79 | 74 | 71 | 77 | 73 | 70 | 68 | | | |
| 5 | 87 | 77 | 71 | 66 | 85 | 76 | 70 | 65 | 74 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 63 | 62 | | | |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | |
| 7 | 77 | 66 | 59 | 54 | 75 | 65 | 59 | 54 | 64 | 58 | 54 | 63 | 57 | 53 | 61 | 57 | 53 | 51 | | | |
| 8 | 72 | 61 | 54 | 49 | 71 | 61 | 54 | 49 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 47 | | | |
| 9 | 68 | 57 | 50 | 45 | 67 | 56 | 50 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 43 | | | |
| 10 | 64 | 53 | 46 | 42 | 63 | 53 | 46 | 42 | 52 | 46 | 42 | 51 | 45 | 42 | 50 | 45 | 41 | 40 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 100779 |
| 5° | 99942 |
| 10° | 98620 |
| 15° | 99747 |
| 20° | 107720 |
| 25° | 117795 |
| 30° | 116370 |
| 35° | 96527 |
| 40° | 56818 |
| 45° | 37116 |
| 50° | 28774 |
| 55° | 19112 |
| 60° | 9300 |
| 65° | 2882 |
| 70° | 974 |
| 75° | 846 |
| 80° | 639 |
| 85° | 1274 |



TEST NUMBER: P584822

CATALOG NUMBER: HC850D010-HM82555835-81WDBB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 305.8 | 5.7 |
| 10°-20° | 897.6 | 16.7 |
| 20°-30° | 1569.5 | 29.2 |
| 30°-40° | 1526.7 | 28.4 |
| 40°-50° | 694.3 | 12.9 |
| 50°-60° | 321.9 | 6.0 |
| 60°-70° | 54.0 | 1.0 |
| 70°-80° | 6.6 | 0.1 |
| 80°-90° | 2.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2772.9 | 51.6 |
| 0°-40° | 4299.6 | 79.9 |
| 0°-60° | 5315.7 | 98.8 |
| 0°-90° | 5378.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5378.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3268 | |
| 5° | 3229 | 306 |
| 15° | 3124 | 898 |
| 25° | 3462 | 1569 |
| 35° | 2564 | 1527 |
| 45° | 851 | 694 |
| 55° | 356 | 322 |
| 65° | 40 | 54 |
| 75° | 7 | 7 |
| 85° | 4 | 2 |
| 90° | 0 | |



TEST NUMBER: P584822

CATALOG NUMBER: HC850D010-HM82555835-81WDBB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3268.2 |
| 2.5° | 3261.0 |
| 5° | 3228.7 |
| 7.5° | 3192.8 |
| 10° | 3149.6 |
| 12.5° | 3117.4 |
| 15° | 3124.5 |
| 17.5° | 3182.0 |
| 20° | 3282.6 |
| 22.5° | 3397.5 |
| 25° | 3462.1 |
| 27.5° | 3426.2 |
| 30° | 3268.2 |
| 32.5° | 2991.6 |
| 35° | 2564.2 |
| 37.5° | 1975.3 |
| 40° | 1411.5 |
| 42.5° | 1052.3 |
| 45° | 851.1 |
| 47.5° | 718.2 |
| 50° | 599.8 |
| 52.5° | 477.7 |
| 55° | 355.5 |
| 57.5° | 244.2 |
| 60° | 150.8 |
| 62.5° | 82.6 |
| 65° | 39.5 |
| 67.5° | 18.0 |
| 70° | 10.8 |
| 72.5° | 7.1 |
| 75° | 7.1 |
| 77.5° | 3.6 |
| 80° | 3.6 |
| 82.5° | 3.6 |
| 85° | 3.6 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)