

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584440

Luminaire Tested: **HC835D010-HM82555927-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584440
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555927-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3179.9 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584440

CATALOG NUMBER: HC835D010-HM82555927-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584440

CATALOG NUMBER: HC835D010-HM82555927-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145421
5°	132518
10°	113224
15°	98741
20°	88004
25°	78065
30°	63918
35°	36707
40°	16291
45°	9481
50°	5469
55°	3124
60°	1727
65°	1102
70°	775
75°	512
80°	391
85°	778



TEST NUMBER: P584440

CATALOG NUMBER: HC835D010-HM82555927-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.5	12.2
10°-20°	869.4	27.3
20°-30°	1040.7	32.7
30°-40°	629.6	19.8
40°-50°	176.4	5.5
50°-60°	54.8	1.7
60°-70°	15.7	0.5
70°-80°	4.3	0.1
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2297.6	72.3
0°-40°	2927.2	92.1
0°-60°	3158.4	99.3
0°-90°	3179.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3179.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4716	
5°	4281	388
15°	3093	869
25°	2294	1041
35°	975	630
45°	217	176
55°	58	55
65°	15	16
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P584440

CATALOG NUMBER: HC835D010-HM82555927-81MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4715.9
2.5°	4582.5
5°	4281.1
7.5°	3941.1
10°	3616.0
12.5°	3331.9
15°	3093.0
17.5°	2882.0
20°	2681.8
22.5°	2496.8
25°	2294.4
27.5°	2066.3
30°	1795.1
32.5°	1444.3
35°	975.1
37.5°	607.0
40°	404.7
42.5°	290.5
45°	217.4
47.5°	159.3
50°	114.0
52.5°	79.7
55°	58.1
57.5°	38.7
60°	28.0
62.5°	19.4
65°	15.1
67.5°	10.8
70°	8.6
72.5°	4.3
75°	4.3
77.5°	2.2
80°	2.2
82.5°	2.2
85°	2.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)