

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584824

Luminaire Tested: **HC850D010-HM82555835-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555835-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5712.7 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584824

CATALOG NUMBER: HC850D010-HM82555835-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584824

CATALOG NUMBER: HC850D010-HM82555835-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130783
5°	127840
10°	123917
15°	121411
20°	120324
25°	118523
30°	112272
35°	93279
40°	54935
45°	36331
50°	28601
55°	21048
60°	14623
65°	8916
70°	3886
75°	1716
80°	1261
85°	0



TEST NUMBER: P584824

CATALOG NUMBER: HC850D010-HM82555835-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.9	6.8
10°-20°	1075.2	18.8
20°-30°	1593.0	27.9
30°-40°	1472.0	25.8
40°-50°	678.7	11.9
50°-60°	357.0	6.2
60°-70°	126.2	2.2
70°-80°	19.8	0.3
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3057.1	53.5
0°-40°	4529.1	79.3
0°-60°	5564.8	97.4
0°-90°	5712.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5712.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4241	
5°	4130	389
15°	3803	1075
25°	3484	1593
35°	2478	1472
45°	833	679
55°	392	357
65°	122	126
75°	14	20
85°	0	2
90°	0	



TEST NUMBER: P584824

CATALOG NUMBER: HC850D010-HM82555835-81WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4241.2
2.5°	4205.4
5°	4130.0
7.5°	4047.3
10°	3957.5
12.5°	3871.4
15°	3803.1
17.5°	3742.1
20°	3666.7
22.5°	3584.0
25°	3483.5
27.5°	3347.1
30°	3153.1
32.5°	2876.6
35°	2477.9
37.5°	1903.4
40°	1364.7
42.5°	1023.5
45°	833.1
47.5°	707.5
50°	596.2
52.5°	488.4
55°	391.5
57.5°	308.8
60°	237.1
62.5°	179.6
65°	122.2
67.5°	71.8
70°	43.1
72.5°	25.1
75°	14.4
77.5°	10.8
80°	7.1
82.5°	3.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)