

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584474

Luminaire Tested: **HC835D010-HM82555935-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555935-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3807.1 lumens
Efficiency: N/A
Efficacy: 113.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584474

CATALOG NUMBER: HC835D010-HM82555935-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584474

CATALOG NUMBER: HC835D010-HM82555935-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174099
5°	158652
10°	135556
15°	118215
20°	105363
25°	93464
30°	76522
35°	43942
40°	19503
45°	11351
50°	6553
55°	3742
60°	2066
65°	1321
70°	929
75°	620
80°	462
85°	920



TEST NUMBER: P584474

CATALOG NUMBER: HC835D010-HM82555935-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	464.0	12.2
10°-20°	1040.9	27.3
20°-30°	1246.0	32.7
30°-40°	753.7	19.8
40°-50°	211.3	5.5
50°-60°	65.6	1.7
60°-70°	18.7	0.5
70°-80°	5.1	0.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2750.8	72.3
0°-40°	3504.5	92.1
0°-60°	3781.4	99.3
0°-90°	3807.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3807.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5646	
5°	5125	464
15°	3703	1041
25°	2747	1246
35°	1167	754
45°	260	211
55°	70	66
65°	18	19
75°	5	5
85°	3	2
90°	0	



TEST NUMBER: P584474

CATALOG NUMBER: HC835D010-HM82555935-81MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5645.9
2.5°	5486.2
5°	5125.4
7.5°	4718.3
10°	4329.2
12.5°	3989.0
15°	3703.0
17.5°	3450.5
20°	3210.8
22.5°	2989.2
25°	2747.0
27.5°	2473.9
30°	2149.1
32.5°	1729.1
35°	1167.3
37.5°	726.7
40°	484.5
42.5°	347.9
45°	260.3
47.5°	190.7
50°	136.6
52.5°	95.4
55°	69.6
57.5°	46.4
60°	33.5
62.5°	23.2
65°	18.1
67.5°	12.9
70°	10.3
72.5°	5.2
75°	5.2
77.5°	2.6
80°	2.6
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)