

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584473

Luminaire Tested: **HC835D010-HM82555935-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555935-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4165.2 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584473

CATALOG NUMBER: HC835D010-HM82555935-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P584473

CATALOG NUMBER: HC835D010-HM82555935-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	73	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248868
5°	237449
10°	205006
15°	156760
20°	119943
25°	94890
30°	71680
35°	38134
40°	14524
45°	6969
50°	2965
55°	1247
60°	481
65°	379
70°	234
75°	0
80°	0
85°	0



TEST NUMBER: P584473

CATALOG NUMBER: HC835D010-HM82555935-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	696.3	16.7
10°-20°	1370.8	32.9
20°-30°	1276.7	30.7
30°-40°	658.8	15.8
40°-50°	134.2	3.2
50°-60°	23.0	0.6
60°-70°	4.5	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3343.8	80.3
0°-40°	4002.6	96.1
0°-60°	4159.7	99.9
0°-90°	4165.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4165.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8071	
5°	7671	696
15°	4910	1371
25°	2789	1277
35°	1013	659
45°	160	134
55°	23	23
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584473

CATALOG NUMBER: HC835D010-HM82555935-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	8070.6
2.5°	7962.3
5°	7671.0
7.5°	7191.6
10°	6547.2
12.5°	5701.6
15°	4910.4
17.5°	4224.7
20°	3655.1
22.5°	3191.1
25°	2788.9
27.5°	2407.5
30°	2013.1
32.5°	1544.0
35°	1013.0
37.5°	587.7
40°	360.8
42.5°	237.1
45°	159.8
47.5°	100.5
50°	61.8
52.5°	36.1
55°	23.2
57.5°	10.3
60°	7.8
62.5°	5.2
65°	5.2
67.5°	2.6
70°	2.6
72.5°	2.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)