

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584830

Luminaire Tested: **HC850D010-HM82555840-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555840-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6284.4 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584830

CATALOG NUMBER: HC850D010-HM82555840-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P584830

CATALOG NUMBER: HC850D010-HM82555840-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	73	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	375485
5°	358257
10°	309306
15°	236516
20°	180963
25°	143170
30°	108152
35°	57535
40°	21918
45°	10519
50°	4476
55°	1882
60°	722
65°	569
70°	352
75°	0
80°	0
85°	0



TEST NUMBER: P584830

CATALOG NUMBER: HC850D010-HM82555840-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1050.6	16.7
10°-20°	2068.3	32.9
20°-30°	1926.2	30.7
30°-40°	993.9	15.8
40°-50°	202.4	3.2
50°-60°	34.6	0.6
60°-70°	6.7	0.1
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5045.1	80.3
0°-40°	6039.1	96.1
0°-60°	6276.1	99.9
0°-90°	6284.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6284.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12177	
5°	11574	###
15°	7409	2068
25°	4208	1926
35°	1528	994
45°	241	202
55°	35	35
65°	8	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P584830

CATALOG NUMBER: HC850D010-HM82555840-81MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	12176.7
2.5°	12013.3
5°	11573.8
7.5°	10850.4
10°	9878.2
12.5°	8602.6
15°	7408.7
17.5°	6374.2
20°	5514.6
22.5°	4814.6
25°	4207.9
27.5°	3632.4
30°	3037.4
32.5°	2329.6
35°	1528.4
37.5°	886.7
40°	544.5
42.5°	357.8
45°	241.2
47.5°	151.6
50°	93.3
52.5°	54.5
55°	35.0
57.5°	15.5
60°	11.7
62.5°	7.8
65°	7.8
67.5°	3.9
70°	3.9
72.5°	3.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)