

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593709

Luminaire Tested: **HC835D010-HM82555950-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555950-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4230.9 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593709

CATALOG NUMBER: HC835D010-HM82555950-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P593709

CATALOG NUMBER: HC835D010-HM82555950-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	796323
5°	510777
10°	230738
15°	139221
20°	106092
25°	85676
30°	62782
35°	22733
40°	8482
45°	3851
50°	1228
55°	312
60°	179
65°	212
70°	0
75°	0
80°	515
85°	1026



TEST NUMBER: P593709

CATALOG NUMBER: HC835D010-HM82555950-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1258.5	29.7
10°-20°	1278.3	30.2
20°-30°	1144.3	27.0
30°-40°	460.9	10.9
40°-50°	75.6	1.8
50°-60°	6.9	0.2
60°-70°	2.5	0.1
70°-80°	1.9	0.0
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3681.1	87.0
0°-40°	4142.0	97.9
0°-60°	4224.5	99.8
0°-90°	4231.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4230.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25824	
5°	16501	###
15°	4361	1278
25°	2518	1144
35°	604	461
45°	88	76
55°	6	7
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P593709

CATALOG NUMBER: HC835D010-HM82555950-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	25824.2
0.5°	25744.4
1°	25411.1
1.5°	24875.6
2°	24063.9
2.5°	23103.9
3°	21901.8
3.5°	20583.0
4°	19278.5
4.5°	17817.1
5°	16501.1
5.5°	15068.3
6°	13906.1
6.5°	12695.6
7°	11744.2
7.5°	10738.8
8°	9929.7
8.5°	9118.0
9°	8508.3
9.5°	7836.1
10°	7369.0
12.5°	5434.8
15°	4361.0
17.5°	3725.8
20°	3233.0
22.5°	2839.9
25°	2518.1
27.5°	2196.2
30°	1763.2
32.5°	1133.7
35°	603.9
37.5°	333.3
40°	210.7
42.5°	139.6
45°	88.3
47.5°	54.1
50°	25.6
52.5°	8.5
55°	5.8
57.5°	2.9
60°	2.9
62.5°	2.9
65°	2.9



TEST NUMBER: P593709

CATALOG NUMBER: HC835D010-HM82555950-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	2.9
80°	2.9
82.5°	2.9
85°	2.9
87.5°	2.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		2.9
70°		0.0



(END OF REPORT)