

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584847

Luminaire Tested: **HC850D010-HM82555927-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584847  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC850D010-HM82555927-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4519.7 lumens  
Efficiency: N/A  
Efficacy: 94.2 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584847

CATALOG NUMBER: HC850D010-HM82555927-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584847

CATALOG NUMBER: HC850D010-HM82555927-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	270046
5°	257659
10°	222453
15°	170101
20°	130152
25°	102971
30°	77783
35°	41378
40°	15763
45°	7562
50°	3219
55°	1349
60°	518
65°	409
70°	252
75°	0
80°	0
85°	0



TEST NUMBER: P584847

CATALOG NUMBER: HC850D010-HM82555927-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	755.6	16.7
10°-20°	1487.5	32.9
20°-30°	1385.4	30.7
30°-40°	714.8	15.8
40°-50°	145.6	3.2
50°-60°	24.9	0.6
60°-70°	4.8	0.1
70°-80°	1.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3628.5	80.3
0°-40°	4343.3	96.1
0°-60°	4513.8	99.9
0°-90°	4519.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4519.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8757	
5°	8324	756
15°	5328	1488
25°	3026	1385
35°	1099	715
45°	173	146
55°	25	25
65°	6	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584847

CATALOG NUMBER: HC850D010-HM82555927-81MDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8757.4
2.5°	8640.0
5°	8323.9
7.5°	7803.7
10°	7104.4
12.5°	6187.0
15°	5328.3
17.5°	4584.4
20°	3966.2
22.5°	3462.7
25°	3026.4
27.5°	2612.4
30°	2184.5
32.5°	1675.4
35°	1099.2
37.5°	637.7
40°	391.6
42.5°	257.3
45°	173.4
47.5°	109.1
50°	67.1
52.5°	39.2
55°	25.1
57.5°	11.2
60°	8.4
62.5°	5.6
65°	5.6
67.5°	2.8
70°	2.8
72.5°	2.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)