

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584867

Luminaire Tested: **HC850D010-HM82555930-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555930-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4945.7 lumens
Efficiency: N/A
Efficacy: 103.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584867

CATALOG NUMBER: HC850D010-HM82555930-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584867

CATALOG NUMBER: HC850D010-HM82555930-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	930902
5°	597102
10°	269734
15°	162749
20°	124022
25°	100150
30°	73393
35°	26577
40°	9919
45°	4500
50°	1434
55°	360
60°	204
65°	241
70°	0
75°	0
80°	586
85°	1168



TEST NUMBER: P584867

CATALOG NUMBER: HC850D010-HM82555930-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1471.2	29.7
10°-20°	1494.3	30.2
20°-30°	1337.7	27.0
30°-40°	538.8	10.9
40°-50°	88.3	1.8
50°-60°	8.0	0.2
60°-70°	2.9	0.1
70°-80°	2.2	0.0
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4303.2	87.0
0°-40°	4842.1	97.9
0°-60°	4938.4	99.9
0°-90°	4946.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4945.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	30188	
5°	19290	###
15°	5098	1494
25°	2944	1338
35°	706	539
45°	103	88
55°	7	8
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584867

CATALOG NUMBER: HC850D010-HM82555930-81NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	30188.5
0.5°	30095.3
1°	29705.7
1.5°	29079.7
2°	28130.7
2.5°	27008.5
3°	25603.3
3.5°	24061.5
4°	22536.4
4.5°	20828.3
5°	19289.9
5.5°	17615.0
6°	16256.3
6.5°	14841.2
7°	13729.0
7.5°	12553.5
8°	11607.9
8.5°	10658.8
9°	9946.3
9.5°	9160.4
10°	8614.4
12.5°	6353.4
15°	5098.0
17.5°	4355.5
20°	3779.4
22.5°	3319.8
25°	2943.5
27.5°	2567.4
30°	2061.2
32.5°	1325.3
35°	706.0
37.5°	389.6
40°	246.4
42.5°	163.2
45°	103.2
47.5°	63.2
50°	29.9
52.5°	9.9
55°	6.7
57.5°	3.3
60°	3.3
62.5°	3.3
65°	3.3



TEST NUMBER: P584867

CATALOG NUMBER: HC850D010-HM82555930-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.3
80°	3.3
82.5°	3.3
85°	3.3
87.5°	3.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.3
70°		0.0



(END OF REPORT)