

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584587

Luminaire Tested: **HC840D010-HM82555927-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584587  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC840D010-HM82555927-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3831.4 lumens  
Efficiency: N/A  
Efficacy: 93.4 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584587

CATALOG NUMBER: HC840D010-HM82555927-81WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584587

CATALOG NUMBER: HC840D010-HM82555927-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76597
5°	76503
10°	75750
15°	74840
20°	74149
25°	73319
30°	69177
35°	56331
40°	31120
45°	20775
50°	18426
55°	17300
60°	17071
65°	16921
70°	15291
75°	13666
80°	11969
85°	10579



TEST NUMBER: P584587

CATALOG NUMBER: HC840D010-HM82555927-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.2	6.1
10°-20°	661.9	17.3
20°-30°	983.6	25.7
30°-40°	885.8	23.1
40°-50°	392.7	10.2
50°-60°	290.8	7.6
60°-70°	226.2	5.9
70°-80°	122.6	3.2
80°-90°	33.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.8	49.1
0°-40°	2765.5	72.2
0°-60°	3449.1	90.0
0°-90°	3831.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3831.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2484	
5°	2472	234
15°	2344	662
25°	2155	984
35°	1496	886
45°	476	393
55°	322	291
65°	232	226
75°	115	123
85°	30	34
90°	0	



TEST NUMBER: P584587

CATALOG NUMBER: HC840D010-HM82555927-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2484.0
2.5°	2479.0
5°	2471.5
7.5°	2451.6
10°	2419.2
12.5°	2381.8
15°	2344.3
17.5°	2306.9
20°	2259.6
22.5°	2212.2
25°	2154.9
27.5°	2067.5
30°	1942.8
32.5°	1763.2
35°	1496.4
37.5°	1117.3
40°	773.1
42.5°	571.1
45°	476.4
47.5°	421.5
50°	384.1
52.5°	349.1
55°	321.8
57.5°	299.3
60°	276.8
62.5°	256.9
65°	231.9
67.5°	202.1
70°	169.6
72.5°	142.2
75°	114.7
77.5°	89.7
80°	67.4
82.5°	47.4
85°	29.9
87.5°	12.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)