

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584648

Luminaire Tested: **HC845D010-HM82555827-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555827-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4409.7 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584648

CATALOG NUMBER: HC845D010-HM82555827-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584648

CATALOG NUMBER: HC845D010-HM82555827-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109913
5°	109618
10°	107792
15°	106218
20°	103670
25°	98411
30°	81169
35°	41789
40°	27981
45°	23989
50°	20700
55°	18069
60°	16053
65°	14425
70°	13073
75°	11783
80°	10548
85°	10508



TEST NUMBER: P584648

CATALOG NUMBER: HC845D010-HM82555827-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.8	7.6
10°-20°	936.1	21.2
20°-30°	1297.0	29.4
30°-40°	779.0	17.7
40°-50°	426.5	9.7
50°-60°	303.0	6.9
60°-70°	196.7	4.5
70°-80°	105.2	2.4
80°-90°	31.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2568.0	58.2
0°-40°	3347.0	75.9
0°-60°	4076.5	92.4
0°-90°	4409.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4409.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3564	
5°	3541	335
15°	3327	936
25°	2892	1297
35°	1110	779
45°	550	426
55°	336	303
65°	198	197
75°	99	105
85°	30	31
90°	0	



TEST NUMBER: P584648

CATALOG NUMBER: HC845D010-HM82555827-81NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3564.4
2.5°	3557.8
5°	3541.3
7.5°	3501.8
10°	3442.5
12.5°	3386.6
15°	3327.2
17.5°	3251.4
20°	3159.2
22.5°	3047.2
25°	2892.4
27.5°	2648.6
30°	2279.6
32.5°	1670.2
35°	1110.1
37.5°	820.3
40°	695.1
42.5°	616.1
45°	550.1
47.5°	487.5
50°	431.5
52.5°	378.9
55°	336.1
57.5°	296.5
60°	260.3
62.5°	227.3
65°	197.7
67.5°	168.0
70°	145.0
72.5°	118.6
75°	98.9
77.5°	79.1
80°	59.4
82.5°	42.8
85°	29.7
87.5°	13.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)