

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584662

Luminaire Tested: **HC845D010-HM82555830-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555830-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4762.7 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584662

CATALOG NUMBER: HC845D010-HM82555830-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584662

CATALOG NUMBER: HC845D010-HM82555830-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54	54	54	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50	50	50	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46	46	46	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	43	43	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40	40	40	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121785
5°	118464
10°	111477
15°	105544
20°	101527
25°	97605
30°	86688
35°	55205
40°	30810
45°	25808
50°	23296
55°	21956
60°	20031
65°	18066
70°	15949
75°	14166
80°	12555
85°	11357



TEST NUMBER: P584662

CATALOG NUMBER: HC845D010-HM82555830-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	356.8	7.5
10°-20°	932.4	19.6
20°-30°	1300.8	27.3
30°-40°	936.0	19.7
40°-50°	463.8	9.7
50°-60°	362.9	7.6
60°-70°	245.7	5.2
70°-80°	127.6	2.7
80°-90°	36.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2590.0	54.4
0°-40°	3525.9	74.0
0°-60°	4352.7	91.4
0°-90°	4762.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4762.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3949	
5°	3827	357
15°	3306	932
25°	2869	1301
35°	1466	936
45°	592	464
55°	408	363
65°	248	246
75°	119	128
85°	32	37
90°	0	



TEST NUMBER: P584662

CATALOG NUMBER: HC845D010-HM82555830-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3949.4
2.5°	3913.9
5°	3827.1
7.5°	3704.9
10°	3560.2
12.5°	3425.2
15°	3306.1
17.5°	3193.6
20°	3093.9
22.5°	2994.2
25°	2868.7
27.5°	2688.6
30°	2434.6
32.5°	2035.7
35°	1466.5
37.5°	1000.2
40°	765.4
42.5°	659.3
45°	591.8
47.5°	533.8
50°	485.6
52.5°	443.9
55°	408.4
57.5°	366.7
60°	324.8
62.5°	283.0
65°	247.6
67.5°	212.3
70°	176.9
72.5°	147.9
75°	118.9
77.5°	93.3
80°	70.7
82.5°	51.5
85°	32.1
87.5°	16.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)