

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593452

Luminaire Tested: **HC805D010-HM80520850-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520850-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 838.9 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593452

CATALOG NUMBER: HC805D010-HM80520850-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593452

CATALOG NUMBER: HC805D010-HM80520850-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19208
5°	18774
10°	18202
15°	17830
20°	17671
25°	17407
30°	16489
35°	13699
40°	8067
45°	5333
50°	4198
55°	3091
60°	2146
65°	1313
70°	568
75°	262
80°	195
85°	0



TEST NUMBER: P593452

CATALOG NUMBER: HC805D010-HM80520850-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	6.8
10°-20°	157.9	18.8
20°-30°	234.0	27.9
30°-40°	216.2	25.8
40°-50°	99.7	11.9
50°-60°	52.4	6.2
60°-70°	18.5	2.2
70°-80°	2.9	0.4
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.0	53.5
0°-40°	665.1	79.3
0°-60°	817.2	97.4
0°-90°	838.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	838.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	623	
5°	606	57
15°	558	158
25°	512	234
35°	364	216
45°	122	100
55°	58	52
65°	18	19
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P593452

CATALOG NUMBER: HC805D010-HM80520850-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	622.9
2.5°	617.7
5°	606.5
7.5°	594.4
10°	581.3
12.5°	568.6
15°	558.5
17.5°	549.5
20°	538.5
22.5°	526.3
25°	511.6
27.5°	491.6
30°	463.1
32.5°	422.4
35°	363.9
37.5°	279.5
40°	200.4
42.5°	150.3
45°	122.3
47.5°	103.9
50°	87.5
52.5°	71.7
55°	57.5
57.5°	45.4
60°	34.8
62.5°	26.3
65°	18.0
67.5°	10.5
70°	6.3
72.5°	3.7
75°	2.2
77.5°	1.6
80°	1.1
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)