

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583500

Luminaire Tested: **HC805D010-HM80520927-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583500  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC805D010-HM80520927-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 577.0 lumens  
Efficiency: N/A  
Efficacy: 96.2 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583500  
CATALOG NUMBER: HC805D010-HM80520927-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P583500

CATALOG NUMBER: HC805D010-HM80520927-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	10811
5°	10719
10°	10577
15°	10701
20°	11558
25°	12633
30°	12484
35°	10356
40°	6094
45°	3982
50°	3085
55°	2054
60°	999
65°	306
70°	108
75°	83
80°	71
85°	142



TEST NUMBER: P583500

CATALOG NUMBER: HC805D010-HM80520927-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.8	5.7
10°-20°	96.3	16.7
20°-30°	168.4	29.2
30°-40°	163.8	28.4
40°-50°	74.5	12.9
50°-60°	34.5	6.0
60°-70°	5.8	1.0
70°-80°	0.7	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	297.4	51.6
0°-40°	461.2	79.9
0°-60°	570.2	98.8
0°-90°	577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	577.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	351	
5°	346	33
15°	335	96
25°	371	168
35°	275	164
45°	91	74
55°	38	35
65°	4	6
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583500

CATALOG NUMBER: HC805D010-HM80520927-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	350.6
2.5°	349.8
5°	346.3
7.5°	342.5
10°	337.8
12.5°	334.3
15°	335.2
17.5°	341.3
20°	352.2
22.5°	364.5
25°	371.3
27.5°	367.5
30°	350.6
32.5°	320.9
35°	275.1
37.5°	211.9
40°	151.4
42.5°	112.9
45°	91.3
47.5°	77.1
50°	64.3
52.5°	51.2
55°	38.2
57.5°	26.2
60°	16.2
62.5°	8.9
65°	4.2
67.5°	1.9
70°	1.2
72.5°	0.7
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)