

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583503

Luminaire Tested: **HC805D010-HM80520927-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520927-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 591.5 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583503

CATALOG NUMBER: HC805D010-HM80520927-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P583503

CATALOG NUMBER: HC805D010-HM80520927-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 111 | 108 | 104 | 101 | 109 | 105 | 102 | 100 | 101 | 99 | 96 | 97 | 95 | 94 | 94 | 92 | 91 | 89 | | | 89 |
| 2 | 104 | 97 | 92 | 87 | 101 | 95 | 90 | 86 | 92 | 88 | 84 | 89 | 85 | 82 | 86 | 83 | 81 | 79 | | | 79 |
| 3 | 97 | 88 | 82 | 76 | 94 | 87 | 81 | 76 | 84 | 79 | 75 | 81 | 77 | 73 | 79 | 75 | 72 | 70 | | | 70 |
| 4 | 90 | 80 | 73 | 68 | 88 | 79 | 73 | 67 | 77 | 71 | 67 | 75 | 70 | 66 | 73 | 68 | 65 | 63 | | | 63 |
| 5 | 84 | 74 | 66 | 61 | 82 | 73 | 66 | 61 | 71 | 65 | 60 | 69 | 64 | 59 | 67 | 63 | 59 | 57 | | | 57 |
| 6 | 79 | 68 | 61 | 55 | 77 | 67 | 60 | 55 | 65 | 59 | 55 | 64 | 58 | 54 | 62 | 58 | 54 | 52 | | | 52 |
| 7 | 74 | 63 | 56 | 50 | 73 | 62 | 55 | 50 | 61 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 49 | 48 | | | 48 |
| 8 | 70 | 58 | 51 | 46 | 69 | 58 | 51 | 46 | 57 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 45 | 44 | | | 44 |
| 9 | 66 | 54 | 47 | 43 | 65 | 54 | 47 | 42 | 53 | 47 | 42 | 52 | 46 | 42 | 51 | 46 | 42 | 40 | | | 40 |
| 10 | 62 | 51 | 44 | 39 | 61 | 50 | 44 | 39 | 49 | 43 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 37 | | | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 11826 |
| 5° | 11812 |
| 10° | 11698 |
| 15° | 11557 |
| 20° | 11449 |
| 25° | 11323 |
| 30° | 10682 |
| 35° | 8696 |
| 40° | 4802 |
| 45° | 3205 |
| 50° | 2845 |
| 55° | 2672 |
| 60° | 2633 |
| 65° | 2612 |
| 70° | 2362 |
| 75° | 2109 |
| 80° | 1847 |
| 85° | 1663 |



TEST NUMBER: P583503

CATALOG NUMBER: HC805D010-HM80520927-81WDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 36.2 | 6.1 |
| 10°-20° | 102.2 | 17.3 |
| 20°-30° | 151.9 | 25.7 |
| 30°-40° | 136.7 | 23.1 |
| 40°-50° | 60.6 | 10.2 |
| 50°-60° | 44.9 | 7.6 |
| 60°-70° | 34.9 | 5.9 |
| 70°-80° | 18.9 | 3.2 |
| 80°-90° | 5.2 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 290.3 | 49.1 |
| 0°-40° | 427.0 | 72.2 |
| 0°-60° | 532.5 | 90.0 |
| 0°-90° | 591.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 591.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 384 | |
| 5° | 382 | 36 |
| 15° | 362 | 102 |
| 25° | 333 | 152 |
| 35° | 231 | 137 |
| 45° | 74 | 61 |
| 55° | 50 | 45 |
| 65° | 36 | 35 |
| 75° | 18 | 19 |
| 85° | 5 | 5 |
| 90° | 0 | |



TEST NUMBER: P583503

CATALOG NUMBER: HC805D010-HM80520927-81WDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 383.5 |
| 2.5° | 382.8 |
| 5° | 381.6 |
| 7.5° | 378.5 |
| 10° | 373.6 |
| 12.5° | 367.7 |
| 15° | 362.0 |
| 17.5° | 356.2 |
| 20° | 348.9 |
| 22.5° | 341.6 |
| 25° | 332.8 |
| 27.5° | 319.2 |
| 30° | 300.0 |
| 32.5° | 272.2 |
| 35° | 231.0 |
| 37.5° | 172.5 |
| 40° | 119.3 |
| 42.5° | 88.2 |
| 45° | 73.5 |
| 47.5° | 65.1 |
| 50° | 59.3 |
| 52.5° | 53.9 |
| 55° | 49.7 |
| 57.5° | 46.2 |
| 60° | 42.7 |
| 62.5° | 39.6 |
| 65° | 35.8 |
| 67.5° | 31.2 |
| 70° | 26.2 |
| 72.5° | 21.9 |
| 75° | 17.7 |
| 77.5° | 13.9 |
| 80° | 10.4 |
| 82.5° | 7.3 |
| 85° | 4.7 |
| 87.5° | 1.9 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)