

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584730

Luminaire Tested: **HC845D010-HM82555930-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555930-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4682.9 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584730

CATALOG NUMBER: HC845D010-HM82555930-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584730

CATALOG NUMBER: HC845D010-HM82555930-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80			
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65			
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59			
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54			
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50			
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119740
5°	116480
10°	109608
15°	103772
20°	99821
25°	95968
30°	85232
35°	54283
40°	30295
45°	25372
50°	22907
55°	21591
60°	19698
65°	17767
70°	15688
75°	13928
80°	12360
85°	11216



TEST NUMBER: P584730

CATALOG NUMBER: HC845D010-HM82555930-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	350.8	7.5
10°-20°	916.8	19.6
20°-30°	1278.9	27.3
30°-40°	920.3	19.7
40°-50°	456.1	9.7
50°-60°	356.8	7.6
60°-70°	241.6	5.2
70°-80°	125.5	2.7
80°-90°	36.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2546.5	54.4
0°-40°	3466.8	74.0
0°-60°	4279.7	91.4
0°-90°	4682.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4682.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3883	
5°	3763	351
15°	3251	917
25°	2821	1279
35°	1442	920
45°	582	456
55°	402	357
65°	244	242
75°	117	125
85°	32	36
90°	0	



TEST NUMBER: P584730

CATALOG NUMBER: HC845D010-HM82555930-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3883.1
2.5°	3848.3
5°	3763.0
7.5°	3642.8
10°	3500.5
12.5°	3367.7
15°	3250.6
17.5°	3140.0
20°	3041.9
22.5°	2944.0
25°	2820.6
27.5°	2643.6
30°	2393.7
32.5°	2001.6
35°	1442.0
37.5°	983.4
40°	752.6
42.5°	648.2
45°	581.8
47.5°	524.9
50°	477.5
52.5°	436.4
55°	401.6
57.5°	360.5
60°	319.4
62.5°	278.2
65°	243.5
67.5°	208.7
70°	174.0
72.5°	145.5
75°	116.9
77.5°	91.7
80°	69.6
82.5°	50.6
85°	31.7
87.5°	15.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)