

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584745

Luminaire Tested: **HC845D010-HM82555935-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555935-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5137.2 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584745
CATALOG NUMBER: HC845D010-HM82555935-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P584745

CATALOG NUMBER: HC845D010-HM82555935-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306945
5°	292863
10°	252845
15°	193342
20°	147935
25°	117036
30°	88408
35°	47033
40°	17913
45°	8595
50°	3656
55°	1538
60°	586
65°	460
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P584745

CATALOG NUMBER: HC845D010-HM82555935-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	858.8	16.7
10°-20°	1690.7	32.9
20°-30°	1574.6	30.7
30°-40°	812.5	15.8
40°-50°	165.5	3.2
50°-60°	28.3	0.6
60°-70°	5.5	0.1
70°-80°	1.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4124.2	80.3
0°-40°	4936.7	96.1
0°-60°	5130.4	99.9
0°-90°	5137.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5137.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9954	
5°	9461	859
15°	6056	1691
25°	3440	1575
35°	1249	812
45°	197	165
55°	29	28
65°	6	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584745

CATALOG NUMBER: HC845D010-HM82555935-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	9954.0
2.5°	9820.5
5°	9461.2
7.5°	8869.9
10°	8075.0
12.5°	7032.3
15°	6056.3
17.5°	5210.6
20°	4508.1
22.5°	3935.8
25°	3439.8
27.5°	2969.3
30°	2482.9
32.5°	1904.4
35°	1249.4
37.5°	724.8
40°	445.0
42.5°	292.4
45°	197.1
47.5°	124.0
50°	76.2
52.5°	44.5
55°	28.6
57.5°	12.7
60°	9.5
62.5°	6.3
65°	6.3
67.5°	3.2
70°	3.2
72.5°	3.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)