

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583528

Luminaire Tested: **HC805D010-HM80520935-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520935-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 669.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583528

CATALOG NUMBER: HC805D010-HM80520935-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583528

CATALOG NUMBER: HC805D010-HM80520935-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87			
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83			
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80			
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76			
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73			
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68			
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125905
5°	80759
10°	36478
15°	22012
20°	16772
25°	13545
30°	9927
35°	3595
40°	1340
45°	611
50°	197
55°	54
60°	31
65°	36
70°	0
75°	0
80°	89
85°	177



TEST NUMBER: P583528

CATALOG NUMBER: HC805D010-HM80520935-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.0	29.7
10°-20°	202.1	30.2
20°-30°	180.9	27.0
30°-40°	72.9	10.9
40°-50°	11.9	1.8
50°-60°	1.1	0.2
60°-70°	0.4	0.1
70°-80°	0.3	0.0
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.0	87.0
0°-40°	654.9	97.9
0°-60°	667.9	99.8
0°-90°	669.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4083	
5°	2609	199
15°	690	202
25°	398	181
35°	96	73
45°	14	12
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P583528

CATALOG NUMBER: HC805D010-HM80520935-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4083.0
0.5°	4070.4
1°	4017.7
1.5°	3933.1
2°	3804.7
2.5°	3652.9
3°	3462.9
3.5°	3254.4
4°	3048.0
4.5°	2817.0
5°	2609.0
5.5°	2382.4
6°	2198.6
6.5°	2007.2
7°	1856.9
7.5°	1697.8
8°	1570.0
8.5°	1441.7
9°	1345.2
9.5°	1239.0
10°	1165.0
12.5°	859.3
15°	689.5
17.5°	589.0
20°	511.1
22.5°	449.0
25°	398.1
27.5°	347.2
30°	278.8
32.5°	179.2
35°	95.5
37.5°	52.7
40°	33.3
42.5°	22.0
45°	14.0
47.5°	8.5
50°	4.1
52.5°	1.3
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P583528

CATALOG NUMBER: HC805D010-HM80520935-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		0.5
70°		0.0



(END OF REPORT)