

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584771

Luminaire Tested: **HC845D010-HM82555940-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555940-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5263.8 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584771

CATALOG NUMBER: HC845D010-HM82555940-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584771

CATALOG NUMBER: HC845D010-HM82555940-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98624
5°	97806
10°	96516
15°	97618
20°	105416
25°	115277
30°	113881
35°	94468
40°	55599
45°	36322
50°	28160
55°	18704
60°	9103
65°	2824
70°	956
75°	834
80°	622
85°	1238



TEST NUMBER: P584771

CATALOG NUMBER: HC845D010-HM82555940-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.2	5.7
10°-20°	878.5	16.7
20°-30°	1535.9	29.2
30°-40°	1494.1	28.4
40°-50°	679.5	12.9
50°-60°	315.0	6.0
60°-70°	52.8	1.0
70°-80°	6.5	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2713.6	51.6
0°-40°	4207.7	79.9
0°-60°	5202.1	98.8
0°-90°	5263.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5263.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3198	
5°	3160	299
15°	3058	878
25°	3388	1536
35°	2510	1494
45°	833	679
55°	348	315
65°	39	53
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P584771

CATALOG NUMBER: HC845D010-HM82555940-81WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3198.3
2.5°	3191.3
5°	3159.7
7.5°	3124.5
10°	3082.4
12.5°	3050.7
15°	3057.8
17.5°	3114.0
20°	3212.4
22.5°	3324.9
25°	3388.1
27.5°	3353.0
30°	3198.3
32.5°	2927.7
35°	2509.5
37.5°	1933.1
40°	1381.2
42.5°	1029.8
45°	832.9
47.5°	703.0
50°	587.0
52.5°	467.4
55°	347.9
57.5°	238.9
60°	147.6
62.5°	80.8
65°	38.7
67.5°	17.6
70°	10.6
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)