

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593472

Luminaire Tested: **HC805D010-HM80520950-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593472
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520950-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 779.3 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593472

CATALOG NUMBER: HC805D010-HM80520950-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P593472

CATALOG NUMBER: HC805D010-HM80520950-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77			
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70			
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59			
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54			
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46			
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18696
5°	18192
10°	18055
15°	17785
20°	17248
25°	16604
30°	15510
35°	12833
40°	7749
45°	5220
50°	3761
55°	2145
60°	944
65°	343
70°	126
75°	60
80°	0
85°	0



TEST NUMBER: P593472

CATALOG NUMBER: HC805D010-HM80520950-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.8	7.2
10°-20°	156.6	20.1
20°-30°	223.3	28.7
30°-40°	203.4	26.1
40°-50°	95.9	12.3
50°-60°	37.7	4.8
60°-70°	6.0	0.8
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.8	55.9
0°-40°	639.1	82.0
0°-60°	772.8	99.2
0°-90°	779.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	779.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	606	
5°	588	56
15°	557	157
25°	488	223
35°	341	203
45°	120	96
55°	40	38
65°	5	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P593472

CATALOG NUMBER: HC805D010-HM80520950-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	606.3
2.5°	598.4
5°	587.7
7.5°	581.7
10°	576.6
12.5°	568.2
15°	557.1
17.5°	543.2
20°	525.6
22.5°	507.0
25°	488.0
27.5°	464.8
30°	435.6
32.5°	396.1
35°	340.9
37.5°	263.5
40°	192.5
42.5°	147.9
45°	119.7
47.5°	98.4
50°	78.4
52.5°	58.9
55°	39.9
57.5°	25.0
60°	15.3
62.5°	9.3
65°	4.7
67.5°	2.3
70°	1.4
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)