

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593773

Luminaire Tested: **HC845D010-HM82555950-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555950-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5190.0 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593773

CATALOG NUMBER: HC845D010-HM82555950-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P593773

CATALOG NUMBER: HC845D010-HM82555950-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237353
5°	216295
10°	184807
15°	161166
20°	143646
25°	127420
30°	104324
35°	59907
40°	26588
45°	15473
50°	8933
55°	5102
60°	2812
65°	1795
70°	1271
75°	834
80°	622
85°	1238



TEST NUMBER: P593773

CATALOG NUMBER: HC845D010-HM82555950-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	632.5	12.2
10°-20°	1419.1	27.3
20°-30°	1698.6	32.7
30°-40°	1027.6	19.8
40°-50°	288.0	5.5
50°-60°	89.4	1.7
60°-70°	25.6	0.5
70°-80°	6.9	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3750.2	72.3
0°-40°	4777.8	92.1
0°-60°	5155.2	99.3
0°-90°	5190.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5190.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7697	
5°	6988	633
15°	5048	1419
25°	3745	1699
35°	1591	1028
45°	355	288
55°	95	89
65°	25	26
75°	7	7
85°	4	2
90°	0	



TEST NUMBER: P593773

CATALOG NUMBER: HC845D010-HM82555950-81MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7697.2
2.5°	7479.4
5°	6987.6
7.5°	6432.5
10°	5902.1
12.5°	5438.3
15°	5048.4
17.5°	4704.1
20°	4377.4
22.5°	4075.2
25°	3745.0
27.5°	3372.6
30°	2929.9
32.5°	2357.3
35°	1591.4
37.5°	990.7
40°	660.5
42.5°	474.2
45°	354.8
47.5°	259.9
50°	186.2
52.5°	130.0
55°	94.9
57.5°	63.2
60°	45.6
62.5°	31.7
65°	24.6
67.5°	17.6
70°	14.1
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)