

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584792

Luminaire Tested: **HC850D010-HM82555827-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555827-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5713.1 lumens
Efficiency: N/A
Efficacy: 119.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584792

CATALOG NUMBER: HC850D010-HM82555827-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584792

CATALOG NUMBER: HC850D010-HM82555827-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100335
5°	99644
10°	99387
15°	101994
20°	110417
25°	118380
30°	115736
35°	96369
40°	59206
45°	40997
50°	31288
55°	20515
60°	12834
65°	9624
70°	9692
75°	11152
80°	12306
85°	11039



TEST NUMBER: P584792

CATALOG NUMBER: HC850D010-HM82555827-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	305.9	5.4
10°-20°	917.1	16.1
20°-30°	1578.9	27.6
30°-40°	1529.7	26.8
40°-50°	753.5	13.2
50°-60°	355.5	6.2
60°-70°	140.1	2.5
70°-80°	96.6	1.7
80°-90°	35.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2801.9	49.0
0°-40°	4331.5	75.8
0°-60°	5440.5	95.2
0°-90°	5713.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5713.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3254	
5°	3219	306
15°	3195	917
25°	3479	1579
35°	2560	1530
45°	940	753
55°	382	356
65°	132	140
75°	94	97
85°	31	36
90°	0	



TEST NUMBER: P584792

CATALOG NUMBER: HC850D010-HM82555827-81WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3253.8
2.5°	3243.4
5°	3219.1
7.5°	3194.9
10°	3174.1
12.5°	3170.6
15°	3194.9
17.5°	3267.7
20°	3364.8
22.5°	3451.6
25°	3479.3
27.5°	3416.9
30°	3250.4
32.5°	2976.3
35°	2560.0
37.5°	1987.7
40°	1470.8
42.5°	1141.3
45°	940.1
47.5°	790.9
50°	652.2
52.5°	513.4
55°	381.6
57.5°	277.5
60°	208.1
62.5°	163.1
65°	131.9
67.5°	114.4
70°	107.5
72.5°	100.7
75°	93.6
77.5°	83.2
80°	69.3
82.5°	52.0
85°	31.2
87.5°	13.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)