

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584941

Luminaire Tested: **HC855D010-HM82555830-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555830-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5311.5 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584941

CATALOG NUMBER: HC855D010-HM82555830-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584941

CATALOG NUMBER: HC855D010-HM82555830-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99518
5°	98691
10°	97390
15°	98499
20°	106371
25°	116322
30°	114914
35°	95323
40°	56102
45°	36658
50°	28409
55°	18876
60°	9189
65°	2846
70°	965
75°	846
80°	622
85°	1238



TEST NUMBER: P584941

CATALOG NUMBER: HC855D010-HM82555830-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.9	5.7
10°-20°	886.4	16.7
20°-30°	1549.8	29.2
30°-40°	1507.6	28.4
40°-50°	685.6	12.9
50°-60°	317.9	6.0
60°-70°	53.3	1.0
70°-80°	6.5	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2738.2	51.6
0°-40°	4245.8	79.9
0°-60°	5249.3	98.8
0°-90°	5311.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5311.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3227	
5°	3188	302
15°	3085	886
25°	3419	1550
35°	2532	1508
45°	841	686
55°	351	318
65°	39	53
75°	7	7
85°	4	2
90°	0	



TEST NUMBER: P584941

CATALOG NUMBER: HC855D010-HM82555830-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3227.3
2.5°	3220.2
5°	3188.3
7.5°	3152.8
10°	3110.3
12.5°	3078.4
15°	3085.4
17.5°	3142.2
20°	3241.5
22.5°	3355.0
25°	3418.8
27.5°	3383.3
30°	3227.3
32.5°	2954.3
35°	2532.2
37.5°	1950.6
40°	1393.7
42.5°	1039.1
45°	840.6
47.5°	709.3
50°	592.2
52.5°	471.7
55°	351.1
57.5°	241.2
60°	149.0
62.5°	81.6
65°	39.0
67.5°	17.7
70°	10.7
72.5°	7.1
75°	7.1
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)