

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584806

Luminaire Tested: **HC850D010-HM82555830-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC850D010-HM82555830-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5690.7 lumens
Efficiency: N/A
Efficacy: 118.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584806

CATALOG NUMBER: HC850D010-HM82555830-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P584806

CATALOG NUMBER: HC850D010-HM82555830-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136531
5°	132858
10°	131852
15°	129886
20°	125952
25°	121255
30°	113265
35°	93730
40°	56589
45°	38119
50°	27464
55°	15661
60°	6895
65°	2474
70°	920
75°	405
80°	0
85°	0



TEST NUMBER: P584806

CATALOG NUMBER: HC850D010-HM82555830-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	407.8	7.2
10°-20°	1143.4	20.1
20°-30°	1631.1	28.7
30°-40°	1485.3	26.1
40°-50°	700.6	12.3
50°-60°	275.5	4.8
60°-70°	43.9	0.8
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3182.3	55.9
0°-40°	4667.5	82.0
0°-60°	5643.7	99.2
0°-90°	5690.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5690.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4428	
5°	4292	408
15°	4069	1143
25°	3564	1631
35°	2490	1485
45°	874	701
55°	291	276
65°	34	44
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P584806

CATALOG NUMBER: HC850D010-HM82555830-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4427.6
2.5°	4370.1
5°	4292.1
7.5°	4248.1
10°	4210.9
12.5°	4149.8
15°	4068.6
17.5°	3966.9
20°	3838.2
22.5°	3702.7
25°	3563.8
27.5°	3394.4
30°	3181.0
32.5°	2893.0
35°	2489.9
37.5°	1924.2
40°	1405.8
42.5°	1080.6
45°	874.1
47.5°	718.2
50°	572.5
52.5°	430.2
55°	291.3
57.5°	182.9
60°	111.8
62.5°	67.8
65°	33.9
67.5°	17.0
70°	10.2
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)