

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584959

Luminaire Tested: **HC855D010-HM82555835-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555835-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6314.3 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584959

CATALOG NUMBER: HC855D010-HM82555835-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P584959

CATALOG NUMBER: HC855D010-HM82555835-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151496
5°	147419
10°	146299
15°	144118
20°	139754
25°	134542
30°	125677
35°	104003
40°	62792
45°	42292
50°	30472
55°	17376
60°	7647
65°	2743
70°	1019
75°	453
80°	0
85°	0



TEST NUMBER: P584959

CATALOG NUMBER: HC855D010-HM82555835-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	452.5	7.2
10°-20°	1268.7	20.1
20°-30°	1809.8	28.7
30°-40°	1648.0	26.1
40°-50°	777.4	12.3
50°-60°	305.7	4.8
60°-70°	48.7	0.8
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3531.0	55.9
0°-40°	5179.0	82.0
0°-60°	6262.1	99.2
0°-90°	6314.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6314.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4913	
5°	4762	452
15°	4514	1269
25°	3954	1810
35°	2763	1648
45°	970	777
55°	323	306
65°	38	49
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P584959

CATALOG NUMBER: HC855D010-HM82555835-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4912.9
2.5°	4848.9
5°	4762.5
7.5°	4713.7
10°	4672.3
12.5°	4604.7
15°	4514.4
17.5°	4401.7
20°	4258.8
22.5°	4108.4
25°	3954.3
27.5°	3766.3
30°	3529.6
32.5°	3210.1
35°	2762.8
37.5°	2135.0
40°	1559.9
42.5°	1199.1
45°	969.8
47.5°	796.8
50°	635.2
52.5°	477.4
55°	323.2
57.5°	203.0
60°	124.0
62.5°	75.1
65°	37.6
67.5°	18.8
70°	11.3
72.5°	3.8
75°	3.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)