

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584971

Luminaire Tested: **HC855D010-HM82555840-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555840-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5450.7 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584971

CATALOG NUMBER: HC855D010-HM82555840-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584971

CATALOG NUMBER: HC855D010-HM82555840-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135862
5°	135498
10°	133239
15°	131294
20°	128144
25°	121643
30°	100333
35°	51659
40°	34586
45°	29654
50°	25589
55°	22333
60°	19840
65°	17833
70°	16157
75°	14547
80°	12999
85°	12985



TEST NUMBER: P584971

CATALOG NUMBER: HC855D010-HM82555840-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	413.9	7.6
10°-20°	1157.1	21.2
20°-30°	1603.2	29.4
30°-40°	963.0	17.7
40°-50°	527.1	9.7
50°-60°	374.5	6.9
60°-70°	243.1	4.5
70°-80°	129.9	2.4
80°-90°	38.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3174.2	58.2
0°-40°	4137.2	75.9
0°-60°	5038.8	92.4
0°-90°	5450.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5450.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4406	
5°	4377	414
15°	4113	1157
25°	3575	1603
35°	1372	963
45°	680	527
55°	415	375
65°	244	243
75°	122	130
85°	37	39
90°	0	



TEST NUMBER: P584971

CATALOG NUMBER: HC855D010-HM82555840-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4405.9
2.5°	4397.7
5°	4377.4
7.5°	4328.5
10°	4255.2
12.5°	4186.0
15°	4112.7
17.5°	4019.0
20°	3905.0
22.5°	3766.6
25°	3575.2
27.5°	3273.9
30°	2817.8
32.5°	2064.5
35°	1372.3
37.5°	1013.9
40°	859.2
42.5°	761.4
45°	680.0
47.5°	602.6
50°	533.4
52.5°	468.3
55°	415.4
57.5°	366.5
60°	321.7
62.5°	280.9
65°	244.4
67.5°	207.7
70°	179.2
72.5°	146.6
75°	122.1
77.5°	97.7
80°	73.2
82.5°	53.0
85°	36.7
87.5°	16.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)