

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593827

Luminaire Tested: **HC855D010-HM82555850-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555850-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6578.3 lumens
Efficiency: N/A
Efficacy: 126.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593827
CATALOG NUMBER: HC855D010-HM82555850-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P593827

CATALOG NUMBER: HC855D010-HM82555850-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			75
6	91	83	78	74	90	82	77	73	81	76	73	79	76	73	78	75	72	71			71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	393043
5°	375012
10°	323772
15°	247575
20°	189430
25°	149866
30°	113208
35°	60227
40°	22941
45°	11007
50°	4687
55°	1973
60°	752
65°	591
70°	370
75°	0
80°	0
85°	0



TEST NUMBER: P593827

CATALOG NUMBER: HC855D010-HM82555850-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1099.7	16.7
10°-20°	2165.0	32.9
20°-30°	2016.3	30.7
30°-40°	1040.4	15.8
40°-50°	211.9	3.2
50°-60°	36.3	0.6
60°-70°	7.0	0.1
70°-80°	1.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5281.0	80.3
0°-40°	6321.5	96.1
0°-60°	6569.7	99.9
0°-90°	6578.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6578.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12746	
5°	12115	###
15°	7755	2165
25°	4405	2016
35°	1600	1040
45°	252	212
55°	37	36
65°	8	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P593827

CATALOG NUMBER: HC855D010-HM82555850-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	12746.1
2.5°	12575.1
5°	12115.1
7.5°	11357.9
10°	10340.2
12.5°	9004.9
15°	7755.1
17.5°	6672.2
20°	5772.6
22.5°	5039.8
25°	4404.7
27.5°	3802.2
30°	3179.4
32.5°	2438.5
35°	1599.9
37.5°	928.2
40°	569.9
42.5°	374.6
45°	252.4
47.5°	158.8
50°	97.7
52.5°	57.0
55°	36.7
57.5°	16.3
60°	12.2
62.5°	8.1
65°	8.1
67.5°	4.1
70°	4.1
72.5°	4.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)