

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585000

Luminaire Tested: **HC855D010-HM82555930-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555930-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5633.8 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585000
CATALOG NUMBER: HC855D010-HM82555930-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P585000

CATALOG NUMBER: HC855D010-HM82555930-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336612
5°	321170
10°	277287
15°	212030
20°	162232
25°	128349
30°	96954
35°	51580
40°	19648
45°	9424
50°	4015
55°	1688
60°	641
65°	503
70°	316
75°	0
80°	0
85°	0



TEST NUMBER: P585000

CATALOG NUMBER: HC855D010-HM82555930-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	941.8	16.7
10°-20°	1854.2	32.9
20°-30°	1726.8	30.7
30°-40°	891.1	15.8
40°-50°	181.5	3.2
50°-60°	31.0	0.6
60°-70°	6.0	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4522.8	80.3
0°-40°	5413.9	96.1
0°-60°	5626.4	99.9
0°-90°	5633.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5633.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10916	
5°	10376	942
15°	6642	1854
25°	3772	1727
35°	1370	891
45°	216	181
55°	31	31
65°	7	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P585000

CATALOG NUMBER: HC855D010-HM82555930-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	10916.1
2.5°	10769.6
5°	10375.7
7.5°	9727.2
10°	8855.6
12.5°	7712.0
15°	6641.7
17.5°	5714.3
20°	4943.8
22.5°	4316.2
25°	3772.3
27.5°	3256.4
30°	2722.9
32.5°	2088.4
35°	1370.2
37.5°	795.0
40°	488.1
42.5°	320.8
45°	216.1
47.5°	136.0
50°	83.7
52.5°	48.8
55°	31.4
57.5°	13.9
60°	10.4
62.5°	6.9
65°	6.9
67.5°	3.5
70°	3.5
72.5°	3.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)