

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585012

Luminaire Tested: **HC855D010-HM82555930-81WDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585012  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC855D010-HM82555930-81WDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5354.9 lumens  
Efficiency: N/A  
Efficacy: 103.0 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585012

CATALOG NUMBER: HC855D010-HM82555930-81WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P585012

CATALOG NUMBER: HC855D010-HM82555930-81WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	107058
5°	106928
10°	105869
15°	104603
20°	103634
25°	102470
30°	96686
35°	78729
40°	43498
45°	29035
50°	25752
55°	24177
60°	23861
65°	23655
70°	21368
75°	19099
80°	16710
85°	14789



TEST NUMBER: P585012

CATALOG NUMBER: HC855D010-HM82555930-81WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	327.4	6.1
10°-20°	925.2	17.3
20°-30°	1374.7	25.7
30°-40°	1238.0	23.1
40°-50°	548.8	10.2
50°-60°	406.5	7.6
60°-70°	316.1	5.9
70°-80°	171.4	3.2
80°-90°	46.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2627.3	49.1
0°-40°	3865.3	72.2
0°-60°	4820.6	90.0
0°-90°	5354.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5354.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3472	
5°	3454	327
15°	3277	925
25°	3012	1375
35°	2091	1238
45°	666	549
55°	450	406
65°	324	316
75°	160	171
85°	42	47
90°	0	



TEST NUMBER: P585012

CATALOG NUMBER: HC855D010-HM82555930-81WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3471.8
2.5°	3464.8
5°	3454.4
7.5°	3426.5
10°	3381.1
12.5°	3328.8
15°	3276.6
17.5°	3224.3
20°	3158.1
22.5°	3091.9
25°	3011.7
27.5°	2889.7
30°	2715.4
32.5°	2464.4
35°	2091.4
37.5°	1561.6
40°	1080.6
42.5°	798.2
45°	665.8
47.5°	589.0
50°	536.8
52.5°	488.0
55°	449.7
57.5°	418.3
60°	386.9
62.5°	359.0
65°	324.2
67.5°	282.3
70°	237.0
72.5°	198.7
75°	160.3
77.5°	125.5
80°	94.1
82.5°	66.2
85°	41.8
87.5°	17.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)