

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585026

Luminaire Tested: **HC855D010-HM82555935-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P585026  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC855D010-HM82555935-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5250.5 lumens  
Efficiency: N/A  
Efficacy: 101.0 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P585026

CATALOG NUMBER: HC855D010-HM82555935-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P585026

CATALOG NUMBER: HC855D010-HM82555935-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62				62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	98377
5°	97558
10°	96272
15°	97369
20°	105147
25°	114988
30°	113596
35°	94231
40°	55462
45°	36230
50°	28083
55°	18655
60°	9078
65°	2816
70°	947
75°	834
80°	622
85°	1238



TEST NUMBER: P585026

CATALOG NUMBER: HC855D010-HM82555935-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	298.5	5.7
10°-20°	876.2	16.7
20°-30°	1532.0	29.2
30°-40°	1490.3	28.4
40°-50°	677.8	12.9
50°-60°	314.2	6.0
60°-70°	52.7	1.0
70°-80°	6.5	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2706.8	51.6
0°-40°	4197.1	79.9
0°-60°	5189.0	98.8
0°-90°	5250.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5250.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3190	
5°	3152	298
15°	3050	876
25°	3380	1532
35°	2503	1490
45°	831	678
55°	347	314
65°	39	53
75°	7	6
85°	4	2
90°	0	



TEST NUMBER: P585026

CATALOG NUMBER: HC855D010-HM82555935-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3190.3
2.5°	3183.3
5°	3151.7
7.5°	3116.7
10°	3074.6
12.5°	3043.0
15°	3050.0
17.5°	3106.2
20°	3204.2
22.5°	3316.5
25°	3379.6
27.5°	3344.5
30°	3190.3
32.5°	2920.4
35°	2503.2
37.5°	1928.2
40°	1377.8
42.5°	1027.3
45°	830.8
47.5°	701.2
50°	585.4
52.5°	466.2
55°	347.0
57.5°	238.4
60°	147.2
62.5°	80.6
65°	38.6
67.5°	17.6
70°	10.5
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	3.5
85°	3.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)