

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583502

Luminaire Tested: **HC805D010-HM80520927-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583502  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC805D010-HM80520927-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 612.9 lumens  
Efficiency: N/A  
Efficacy: 102.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583502

CATALOG NUMBER: HC805D010-HM80520927-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P583502

CATALOG NUMBER: HC805D010-HM80520927-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	63	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	14031
5°	13713
10°	13292
15°	13022
20°	12906
25°	12715
30°	12046
35°	10010
40°	5893
45°	3899
50°	3065
55°	2258
60°	1566
65°	949
70°	424
75°	191
80°	124
85°	0



TEST NUMBER: P583502

CATALOG NUMBER: HC805D010-HM80520927-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.7	6.8
10°-20°	115.3	18.8
20°-30°	170.9	27.9
30°-40°	157.9	25.8
40°-50°	72.8	11.9
50°-60°	38.3	6.2
60°-70°	13.5	2.2
70°-80°	2.2	0.4
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.9	53.5
0°-40°	485.9	79.3
0°-60°	597.0	97.4
0°-90°	612.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	612.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	455	
5°	443	42
15°	408	115
25°	374	171
35°	266	158
45°	89	73
55°	42	38
65°	13	14
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P583502

CATALOG NUMBER: HC805D010-HM80520927-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	455.0
2.5°	451.1
5°	443.0
7.5°	434.2
10°	424.5
12.5°	415.2
15°	407.9
17.5°	401.4
20°	393.3
22.5°	384.5
25°	373.7
27.5°	359.0
30°	338.3
32.5°	308.6
35°	265.9
37.5°	204.2
40°	146.4
42.5°	109.8
45°	89.4
47.5°	75.9
50°	63.9
52.5°	52.4
55°	42.0
57.5°	33.2
60°	25.4
62.5°	19.3
65°	13.0
67.5°	7.7
70°	4.7
72.5°	2.8
75°	1.6
77.5°	1.2
80°	0.7
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)