

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585068

Luminaire Tested: **HC860D010-HM86080830-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080830-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5593.5 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585068

CATALOG NUMBER: HC860D010-HM86080830-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P585068

CATALOG NUMBER: HC860D010-HM86080830-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	334204
5°	318874
10°	275305
15°	210514
20°	161071
25°	127430
30°	96263
35°	51211
40°	19511
45°	9359
50°	3982
55°	1672
60°	641
65°	503
70°	316
75°	0
80°	0
85°	0



TEST NUMBER: P585068

CATALOG NUMBER: HC860D010-HM86080830-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	935.1	16.7
10°-20°	1840.9	32.9
20°-30°	1714.5	30.7
30°-40°	884.7	15.8
40°-50°	180.2	3.2
50°-60°	30.8	0.6
60°-70°	6.0	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4490.5	80.3
0°-40°	5375.2	96.1
0°-60°	5586.2	99.9
0°-90°	5593.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5593.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10838	
5°	10302	935
15°	6594	1841
25°	3745	1714
35°	1360	885
45°	215	180
55°	31	31
65°	7	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P585068

CATALOG NUMBER: HC860D010-HM86080830-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	10838.0
2.5°	10692.6
5°	10301.5
7.5°	9657.6
10°	8792.3
12.5°	7656.8
15°	6594.2
17.5°	5673.5
20°	4908.4
22.5°	4285.3
25°	3745.3
27.5°	3233.1
30°	2703.5
32.5°	2073.5
35°	1360.4
37.5°	789.3
40°	484.7
42.5°	318.5
45°	214.6
47.5°	134.9
50°	83.0
52.5°	48.4
55°	31.1
57.5°	13.8
60°	10.4
62.5°	6.9
65°	6.9
67.5°	3.5
70°	3.5
72.5°	3.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)