

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583509

Luminaire Tested: **HC805D010-HM80520930-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520930-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 630.1 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583509

CATALOG NUMBER: HC805D010-HM80520930-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P583509

CATALOG NUMBER: HC805D010-HM80520930-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28813
5°	26255
10°	22432
15°	19566
20°	17435
25°	15467
30°	12662
35°	7273
40°	3228
45°	1880
50°	1084
55°	618
60°	339
65°	219
70°	153
75°	95
80°	89
85°	177



TEST NUMBER: P583509

CATALOG NUMBER: HC805D010-HM80520930-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	12.2
10°-20°	172.3	27.3
20°-30°	206.2	32.7
30°-40°	124.8	19.8
40°-50°	35.0	5.6
50°-60°	10.9	1.7
60°-70°	3.1	0.5
70°-80°	0.8	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	455.2	72.2
0°-40°	580.0	92.0
0°-60°	625.8	99.3
0°-90°	630.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	630.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	934	
5°	848	77
15°	613	172
25°	455	206
35°	193	125
45°	43	35
55°	12	11
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583509

CATALOG NUMBER: HC805D010-HM80520930-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	934.4
2.5°	907.9
5°	848.2
7.5°	780.8
10°	716.4
12.5°	660.1
15°	612.9
17.5°	571.0
20°	531.3
22.5°	494.7
25°	454.6
27.5°	409.4
30°	355.6
32.5°	286.2
35°	193.2
37.5°	120.3
40°	80.2
42.5°	57.6
45°	43.1
47.5°	31.6
50°	22.6
52.5°	15.8
55°	11.5
57.5°	7.7
60°	5.5
62.5°	3.8
65°	3.0
67.5°	2.2
70°	1.7
72.5°	0.8
75°	0.8
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)