

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P585102

Luminaire Tested: **HC860D010-HM86080840-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P585102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080840-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7045.4 lumens
Efficiency: N/A
Efficacy: 125.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P585102

CATALOG NUMBER: HC860D010-HM86080840-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P585102

CATALOG NUMBER: HC860D010-HM86080840-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			
6	91	83	78	74	90	82	77	73	81	76	73	79	76	73	78	75	72	71			
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	420950
5°	401639
10°	346759
15°	265152
20°	202881
25°	160509
30°	121248
35°	64503
40°	24571
45°	11792
50°	5018
55°	2107
60°	802
65°	642
70°	397
75°	0
80°	0
85°	0



TEST NUMBER: P585102

CATALOG NUMBER: HC860D010-HM86080840-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1177.8	16.7
10°-20°	2318.7	32.9
20°-30°	2159.5	30.7
30°-40°	1114.3	15.8
40°-50°	227.0	3.2
50°-60°	38.8	0.6
60°-70°	7.6	0.1
70°-80°	1.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5656.0	80.3
0°-40°	6770.3	96.1
0°-60°	7036.1	99.9
0°-90°	7045.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7045.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13651	
5°	12975	###
15°	8306	2319
25°	4718	2160
35°	1714	1114
45°	270	227
55°	39	39
65°	9	8
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P585102

CATALOG NUMBER: HC860D010-HM86080840-81MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	13651.1
2.5°	13467.9
5°	12975.3
7.5°	12164.3
10°	11074.3
12.5°	9644.3
15°	8305.7
17.5°	7146.0
20°	6182.5
22.5°	5397.7
25°	4717.5
27.5°	4072.2
30°	3405.2
32.5°	2611.6
35°	1713.5
37.5°	994.1
40°	610.4
42.5°	401.2
45°	270.4
47.5°	170.0
50°	104.6
52.5°	61.0
55°	39.2
57.5°	17.4
60°	13.0
62.5°	8.8
65°	8.8
67.5°	4.4
70°	4.4
72.5°	4.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)