

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593471

Luminaire Tested: **HC805D010-HM80520950-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520950-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 688.9 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593471

CATALOG NUMBER: HC805D010-HM80520950-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P593471

CATALOG NUMBER: HC805D010-HM80520950-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96		
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91		
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87		
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83		
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80		
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68		
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129642
5°	83155
10°	37562
15°	22663
20°	17271
25°	13950
30°	10219
35°	3700
40°	1385
45°	628
50°	201
55°	54
60°	31
65°	36
70°	0
75°	0
80°	89
85°	177



TEST NUMBER: P593471

CATALOG NUMBER: HC805D010-HM80520950-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	204.9	29.7
10°-20°	208.1	30.2
20°-30°	186.3	27.0
30°-40°	75.0	10.9
40°-50°	12.3	1.8
50°-60°	1.2	0.2
60°-70°	0.4	0.1
70°-80°	0.3	0.0
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.3	87.0
0°-40°	674.3	97.9
0°-60°	687.8	99.8
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	688.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4204	
5°	2686	205
15°	710	208
25°	410	186
35°	98	75
45°	14	12
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P593471

CATALOG NUMBER: HC805D010-HM80520950-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4204.2
0.5°	4191.2
1°	4137.0
1.5°	4049.8
2°	3917.7
2.5°	3761.3
3°	3565.6
3.5°	3350.9
4°	3138.5
4.5°	2900.7
5°	2686.4
5.5°	2453.1
6°	2263.9
6.5°	2066.9
7°	1912.0
7.5°	1748.2
8°	1616.5
8.5°	1484.4
9°	1385.2
9.5°	1275.8
10°	1199.6
12.5°	884.8
15°	709.9
17.5°	606.5
20°	526.3
22.5°	462.4
25°	410.0
27.5°	357.5
30°	287.0
32.5°	184.6
35°	98.3
37.5°	54.2
40°	34.4
42.5°	22.7
45°	14.4
47.5°	8.9
50°	4.2
52.5°	1.4
55°	1.0
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P593471

CATALOG NUMBER: HC805D010-HM80520950-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		0.5
70°		0.0



(END OF REPORT)