

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593860

Luminaire Tested: **HC860D010-HM86080850-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC860D010-HM86080850-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6936.4 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 56
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593860

CATALOG NUMBER: HC860D010-HM86080850-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593860

CATALOG NUMBER: HC860D010-HM86080850-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158798
5°	155219
10°	150464
15°	147419
20°	146097
25°	143908
30°	136320
35°	113264
40°	66701
45°	44115
50°	34728
55°	25553
60°	17749
65°	10813
70°	4724
75°	2073
80°	1563
85°	0



TEST NUMBER: P593860

CATALOG NUMBER: HC860D010-HM86080850-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.2	6.8
10°-20°	1305.5	18.8
20°-30°	1934.2	27.9
30°-40°	1787.3	25.8
40°-50°	824.1	11.9
50°-60°	433.5	6.2
60°-70°	153.2	2.2
70°-80°	24.1	0.3
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3711.9	53.5
0°-40°	5499.2	79.3
0°-60°	6756.8	97.4
0°-90°	6936.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6936.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5150	
5°	5014	472
15°	4618	1306
25°	4230	1934
35°	3009	1787
45°	1012	824
55°	475	433
65°	148	153
75°	17	24
85°	0	2
90°	0	



TEST NUMBER: P593860

CATALOG NUMBER: HC860D010-HM86080850-81WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5149.7
2.5°	5106.1
5°	5014.5
7.5°	4914.3
10°	4805.3
12.5°	4700.6
15°	4617.8
17.5°	4543.6
20°	4452.1
22.5°	4351.8
25°	4229.6
27.5°	4064.0
30°	3828.5
32.5°	3492.7
35°	3008.8
37.5°	2311.1
40°	1657.0
42.5°	1242.8
45°	1011.6
47.5°	859.1
50°	723.9
52.5°	593.1
55°	475.3
57.5°	375.0
60°	287.8
62.5°	218.0
65°	148.2
67.5°	87.2
70°	52.4
72.5°	30.6
75°	17.4
77.5°	13.0
80°	8.8
82.5°	4.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)