

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584918

Luminaire Tested: **HC855D010-HM82555827-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555827-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5392.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584918

CATALOG NUMBER: HC855D010-HM82555827-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584918

CATALOG NUMBER: HC855D010-HM82555827-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1014891
5°	650974
10°	294070
15°	177434
20°	135212
25°	109190
30°	80015
35°	28975
40°	10812
45°	4906
50°	1569
55°	392
60°	222
65°	263
70°	0
75°	0
80°	639
85°	1274



TEST NUMBER: P584918

CATALOG NUMBER: HC855D010-HM82555827-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1603.9	29.7
10°-20°	1629.2	30.2
20°-30°	1458.4	27.0
30°-40°	587.4	10.9
40°-50°	96.3	1.8
50°-60°	8.8	0.2
60°-70°	3.1	0.1
70°-80°	2.4	0.0
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4691.5	87.0
0°-40°	5278.9	97.9
0°-60°	5384.0	99.9
0°-90°	5392.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5392.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	32912	
5°	21030	###
15°	5558	1629
25°	3209	1458
35°	770	587
45°	112	96
55°	7	9
65°	4	3
75°	0	2
85°	4	3
90°	0	



TEST NUMBER: P584918

CATALOG NUMBER: HC855D010-HM82555827-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	32912.2
0.5°	32810.6
1°	32385.8
1.5°	31703.3
2°	30668.7
2.5°	29445.3
3°	27913.3
3.5°	26232.5
4°	24569.8
4.5°	22707.5
5°	21030.3
5.5°	19204.3
6°	17723.1
6.5°	16180.2
7°	14967.7
7.5°	13686.1
8°	12655.1
8.5°	11620.5
9°	10843.7
9.5°	9987.0
10°	9391.6
12.5°	6926.6
15°	5558.0
17.5°	4748.5
20°	4120.4
22.5°	3619.4
25°	3209.2
27.5°	2799.0
30°	2247.2
32.5°	1444.8
35°	769.7
37.5°	424.7
40°	268.6
42.5°	177.9
45°	112.5
47.5°	69.0
50°	32.7
52.5°	10.9
55°	7.3
57.5°	3.6
60°	3.6
62.5°	3.6
65°	3.6



TEST NUMBER: P584918

CATALOG NUMBER: HC855D010-HM82555827-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.6
80°	3.6
82.5°	3.6
85°	3.6
87.5°	3.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.6
70°		0.0



(END OF REPORT)