

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584937

Luminaire Tested: **HC855D010-HM82555830-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584937
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555830-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4747.7 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584937

CATALOG NUMBER: HC855D010-HM82555830-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584937

CATALOG NUMBER: HC855D010-HM82555830-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118341
5°	118025
10°	116055
15°	114362
20°	111618
25°	105954
30°	87393
35°	44996
40°	30126
45°	25830
50°	22288
55°	19451
60°	17281
65°	15527
70°	14074
75°	12677
80°	11347
85°	11286



TEST NUMBER: P584937

CATALOG NUMBER: HC855D010-HM82555830-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.5	7.6
10°-20°	1007.9	21.2
20°-30°	1396.5	29.4
30°-40°	838.8	17.7
40°-50°	459.2	9.7
50°-60°	326.2	6.9
60°-70°	211.7	4.5
70°-80°	113.1	2.4
80°-90°	33.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2764.9	58.2
0°-40°	3603.6	75.9
0°-60°	4389.0	92.4
0°-90°	4747.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4747.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3838	
5°	3813	361
15°	3582	1008
25°	3114	1396
35°	1195	839
45°	592	459
55°	362	326
65°	213	212
75°	106	113
85°	32	34
90°	0	



TEST NUMBER: P584937

CATALOG NUMBER: HC855D010-HM82555830-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3837.7
2.5°	3830.6
5°	3812.9
7.5°	3770.3
10°	3706.4
12.5°	3646.2
15°	3582.3
17.5°	3500.8
20°	3401.4
22.5°	3280.9
25°	3114.1
27.5°	2851.7
30°	2454.4
32.5°	1798.2
35°	1195.3
37.5°	883.2
40°	748.4
42.5°	663.2
45°	592.3
47.5°	524.9
50°	464.6
52.5°	407.9
55°	361.8
57.5°	319.3
60°	280.2
62.5°	244.7
65°	212.8
67.5°	180.8
70°	156.1
72.5°	127.6
75°	106.4
77.5°	85.1
80°	63.9
82.5°	46.1
85°	31.9
87.5°	14.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)