

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584960

Luminaire Tested: **HC855D010-HM82555835-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555835-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5979.9 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584960

CATALOG NUMBER: HC855D010-HM82555835-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584960

CATALOG NUMBER: HC855D010-HM82555835-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136904
5°	133815
10°	129716
15°	127090
20°	125952
25°	124066
30°	117524
35°	97645
40°	57507
45°	38032
50°	29935
55°	22026
60°	15301
65°	9332
70°	4066
75°	1787
80°	1332
85°	0



TEST NUMBER: P584960

CATALOG NUMBER: HC855D010-HM82555835-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	407.1	6.8
10°-20°	1125.5	18.8
20°-30°	1667.5	27.9
30°-40°	1540.8	25.8
40°-50°	710.4	11.9
50°-60°	373.6	6.2
60°-70°	132.1	2.2
70°-80°	20.8	0.3
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3200.1	53.5
0°-40°	4740.9	79.3
0°-60°	5825.0	97.4
0°-90°	5979.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5979.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4440	
5°	4323	407
15°	3981	1125
25°	3646	1667
35°	2594	1541
45°	872	710
55°	410	374
65°	128	132
75°	15	21
85°	0	2
90°	0	



TEST NUMBER: P584960

CATALOG NUMBER: HC855D010-HM82555835-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4439.7
2.5°	4402.0
5°	4323.0
7.5°	4236.7
10°	4142.7
12.5°	4052.4
15°	3981.0
17.5°	3917.1
20°	3838.2
22.5°	3751.7
25°	3646.4
27.5°	3503.6
30°	3300.6
32.5°	3011.1
35°	2593.9
37.5°	1992.4
40°	1428.6
42.5°	1071.3
45°	872.1
47.5°	740.6
50°	624.0
52.5°	511.2
55°	409.7
57.5°	323.2
60°	248.1
62.5°	188.0
65°	127.9
67.5°	75.2
70°	45.1
72.5°	26.4
75°	15.0
77.5°	11.3
80°	7.5
82.5°	3.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)