

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584975

Luminaire Tested: **HC855D010-HM82555840-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555840-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6097.9 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584975

CATALOG NUMBER: HC855D010-HM82555840-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584975

CATALOG NUMBER: HC855D010-HM82555840-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 93 | 92 | | | |
| 2 | 106 | 100 | 95 | 92 | 104 | 98 | 94 | 91 | 95 | 92 | 89 | 92 | 89 | 87 | 89 | 87 | 85 | 83 | | | |
| 3 | 99 | 92 | 86 | 81 | 97 | 90 | 85 | 81 | 88 | 83 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 75 | | | |
| 4 | 93 | 84 | 78 | 73 | 91 | 83 | 77 | 72 | 81 | 76 | 71 | 79 | 74 | 71 | 77 | 73 | 70 | 68 | | | |
| 5 | 87 | 77 | 71 | 66 | 85 | 76 | 70 | 65 | 74 | 69 | 65 | 73 | 68 | 64 | 71 | 67 | 63 | 62 | | | |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | |
| 7 | 77 | 66 | 59 | 54 | 75 | 65 | 59 | 54 | 64 | 58 | 54 | 63 | 57 | 53 | 61 | 57 | 53 | 51 | | | |
| 8 | 72 | 61 | 54 | 49 | 71 | 61 | 54 | 49 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 52 | 49 | 47 | | | |
| 9 | 68 | 57 | 50 | 45 | 67 | 56 | 50 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 43 | | | |
| 10 | 64 | 53 | 46 | 42 | 63 | 53 | 46 | 42 | 52 | 46 | 42 | 51 | 45 | 42 | 50 | 45 | 41 | 40 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 114255 |
| 5° | 113304 |
| 10° | 111806 |
| 15° | 113085 |
| 20° | 122122 |
| 25° | 133545 |
| 30° | 131930 |
| 35° | 109435 |
| 40° | 64410 |
| 45° | 42078 |
| 50° | 32621 |
| 55° | 21671 |
| 60° | 10546 |
| 65° | 3269 |
| 70° | 1100 |
| 75° | 965 |
| 80° | 728 |
| 85° | 1451 |



TEST NUMBER: P584975

CATALOG NUMBER: HC855D010-HM82555840-81WDBB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 346.6 | 5.7 |
| 10°-20° | 1017.7 | 16.7 |
| 20°-30° | 1779.3 | 29.2 |
| 30°-40° | 1730.8 | 28.4 |
| 40°-50° | 787.1 | 12.9 |
| 50°-60° | 364.9 | 6.0 |
| 60°-70° | 61.2 | 1.0 |
| 70°-80° | 7.5 | 0.1 |
| 80°-90° | 2.8 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3143.6 | 51.6 |
| 0°-40° | 4874.4 | 79.9 |
| 0°-60° | 6026.5 | 98.8 |
| 0°-90° | 6097.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6097.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3705 | |
| 5° | 3660 | 347 |
| 15° | 3542 | 1018 |
| 25° | 3925 | 1779 |
| 35° | 2907 | 1731 |
| 45° | 965 | 787 |
| 55° | 403 | 365 |
| 65° | 45 | 61 |
| 75° | 8 | 7 |
| 85° | 4 | 3 |
| 90° | 0 | |



TEST NUMBER: P584975

CATALOG NUMBER: HC855D010-HM82555840-81WDBB

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3705.2 |
| 2.5° | 3697.0 |
| 5° | 3660.4 |
| 7.5° | 3619.6 |
| 10° | 3570.7 |
| 12.5° | 3534.2 |
| 15° | 3542.3 |
| 17.5° | 3607.4 |
| 20° | 3721.5 |
| 22.5° | 3851.7 |
| 25° | 3925.0 |
| 27.5° | 3884.2 |
| 30° | 3705.2 |
| 32.5° | 3391.7 |
| 35° | 2907.1 |
| 37.5° | 2239.3 |
| 40° | 1600.1 |
| 42.5° | 1193.0 |
| 45° | 964.9 |
| 47.5° | 814.3 |
| 50° | 680.0 |
| 52.5° | 541.5 |
| 55° | 403.1 |
| 57.5° | 276.8 |
| 60° | 171.0 |
| 62.5° | 93.6 |
| 65° | 44.8 |
| 67.5° | 20.4 |
| 70° | 12.2 |
| 72.5° | 8.1 |
| 75° | 8.1 |
| 77.5° | 4.1 |
| 80° | 4.1 |
| 82.5° | 4.1 |
| 85° | 4.1 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)