

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583579

Luminaire Tested: **HC807D010-HM80520830-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520830-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 924.3 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583579

CATALOG NUMBER: HC807D010-HM80520830-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583579

CATALOG NUMBER: HC807D010-HM80520830-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	173985
5°	111599
10°	50412
15°	30417
20°	23181
25°	18720
30°	13719
35°	4965
40°	1852
45°	837
50°	269
55°	65
60°	37
65°	44
70°	0
75°	0
80°	107
85°	212



TEST NUMBER: P583579

CATALOG NUMBER: HC807D010-HM80520830-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.0	29.7
10°-20°	279.3	30.2
20°-30°	250.0	27.0
30°-40°	100.7	10.9
40°-50°	16.5	1.8
50°-60°	1.5	0.2
60°-70°	0.5	0.1
70°-80°	0.4	0.0
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	804.3	87.0
0°-40°	905.0	97.9
0°-60°	922.9	99.9
0°-90°	924.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	924.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5642	
5°	3605	275
15°	953	279
25°	550	250
35°	132	101
45°	19	16
55°	1	1
65°	1	1
75°	0	0
85°	1	1
90°	0	



TEST NUMBER: P583579

CATALOG NUMBER: HC807D010-HM80520830-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	5642.2
0.5°	5624.7
1°	5552.0
1.5°	5435.0
2°	5257.6
2.5°	5047.9
3°	4785.3
3.5°	4497.1
4°	4212.0
4.5°	3892.8
5°	3605.3
5.5°	3292.2
6°	3038.3
6.5°	2773.8
7°	2565.9
7.5°	2346.3
8°	2169.5
8.5°	1992.2
9°	1858.9
9.5°	1712.1
10°	1610.0
12.5°	1187.5
15°	952.8
17.5°	814.0
20°	706.4
22.5°	620.4
25°	550.2
27.5°	479.8
30°	385.3
32.5°	247.7
35°	131.9
37.5°	72.8
40°	46.0
42.5°	30.5
45°	19.2
47.5°	11.8
50°	5.6
52.5°	1.9
55°	1.2
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P583579

CATALOG NUMBER: HC807D010-HM80520830-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		0.6
70°		0.0



(END OF REPORT)