

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583597

Luminaire Tested: **HC807D010-HM80520835-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520835-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 876.7 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583597

CATALOG NUMBER: HC807D010-HM80520835-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P583597

CATALOG NUMBER: HC807D010-HM80520835-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84			84
4	100	93	88	84	98	92	88	84	90	86	83	88	85	82	86	83	81	80			80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75			75
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72			72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68			68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65			65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62			62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69767
5°	59107
10°	42885
15°	32205
20°	25412
25°	20496
30°	15190
35°	6155
40°	2596
45°	1391
50°	624
55°	317
60°	197
65°	139
70°	117
75°	71
80°	107
85°	212



TEST NUMBER: P583597

CATALOG NUMBER: HC807D010-HM80520835-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.0	18.7
10°-20°	283.3	32.3
20°-30°	274.0	31.2
30°-40°	120.3	13.7
40°-50°	26.0	3.0
50°-60°	5.8	0.7
60°-70°	2.0	0.2
70°-80°	0.7	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.2	82.3
0°-40°	841.6	96.0
0°-60°	873.4	99.6
0°-90°	876.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	876.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2262	
5°	1910	164
15°	1009	283
25°	602	274
35°	164	120
45°	32	26
55°	6	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P583597

CATALOG NUMBER: HC807D010-HM80520835-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2262.5
1°	2245.6
2°	2199.4
3°	2116.0
4°	2016.3
5°	1909.5
6°	1793.0
7°	1675.7
8°	1565.7
9°	1463.4
10°	1369.6
11°	1281.0
12°	1201.6
13°	1129.3
14°	1065.5
15°	1008.8
17.5°	881.8
20°	774.4
22.5°	680.0
25°	602.4
27.5°	523.6
30°	426.6
32.5°	289.8
35°	163.5
37.5°	96.4
40°	64.5
42.5°	45.6
45°	31.9
47.5°	20.8
50°	13.0
52.5°	7.8
55°	5.9
57.5°	4.5
60°	3.2
62.5°	2.6
65°	1.9
67.5°	1.3
70°	1.3
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6



TEST NUMBER: P583597

CATALOG NUMBER: HC807D010-HM80520835-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°		0.6
87.5°		0.6



(END OF REPORT)