

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593484

Luminaire Tested: **HC807D010-HM80520850-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520850-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1027.6 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593484

CATALOG NUMBER: HC807D010-HM80520850-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P593484

CATALOG NUMBER: HC807D010-HM80520850-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46995
5°	42828
10°	36591
15°	31908
20°	28441
25°	25229
30°	20659
35°	11862
40°	5261
45°	3066
50°	1770
55°	1011
60°	561
65°	358
70°	243
75°	167
80°	124
85°	248



TEST NUMBER: P593484

CATALOG NUMBER: HC807D010-HM80520850-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.2	12.2
10°-20°	281.0	27.3
20°-30°	336.3	32.7
30°-40°	203.5	19.8
40°-50°	57.0	5.5
50°-60°	17.7	1.7
60°-70°	5.0	0.5
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	742.5	72.3
0°-40°	946.0	92.1
0°-60°	1020.7	99.3
0°-90°	1027.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1524	
5°	1384	125
15°	1000	281
25°	742	336
35°	315	203
45°	70	57
55°	19	18
65°	5	5
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P593484

CATALOG NUMBER: HC807D010-HM80520850-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1524.0
2.5°	1480.8
5°	1383.6
7.5°	1273.6
10°	1168.6
12.5°	1076.8
15°	999.5
17.5°	931.4
20°	866.7
22.5°	806.9
25°	741.5
27.5°	667.8
30°	580.2
32.5°	466.8
35°	315.1
37.5°	196.1
40°	130.7
42.5°	93.9
45°	70.3
47.5°	51.5
50°	36.9
52.5°	25.7
55°	18.8
57.5°	12.5
60°	9.1
62.5°	6.2
65°	4.9
67.5°	3.5
70°	2.7
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)