

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593485

Luminaire Tested: **HC807D010-HM80520850-81NDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593485  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC807D010-HM80520850-81NDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 942.1 lumens  
Efficiency: N/A  
Efficacy: 117.8 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593485

CATALOG NUMBER: HC807D010-HM80520850-81NDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593485

CATALOG NUMBER: HC807D010-HM80520850-81NDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84			84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80			80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75			75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72			72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68			68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65			65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62			62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59			59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	74960
5°	63505
10°	46076
15°	34603
20°	27302
25°	22020
30°	16319
35°	6614
40°	2790
45°	1496
50°	672
55°	339
60°	216
65°	161
70°	126
75°	83
80°	124
85°	248



TEST NUMBER: P593485

CATALOG NUMBER: HC807D010-HM80520850-81NDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	176.1	18.7
10°-20°	304.4	32.3
20°-30°	294.3	31.2
30°-40°	129.3	13.7
40°-50°	27.9	3.0
50°-60°	6.3	0.7
60°-70°	2.2	0.2
70°-80°	0.8	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	774.9	82.3
0°-40°	904.2	96.0
0°-60°	938.4	99.6
0°-90°	942.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2431	
5°	2052	176
15°	1084	304
25°	647	294
35°	176	129
45°	34	28
55°	6	6
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P593485

CATALOG NUMBER: HC807D010-HM80520850-81NDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2430.9
1°	2412.6
2°	2363.0
3°	2273.4
4°	2166.3
5°	2051.6
6°	1926.3
7°	1800.4
8°	1682.1
9°	1572.3
10°	1471.5
11°	1376.4
12°	1291.0
13°	1213.3
14°	1144.7
15°	1083.9
17.5°	947.4
20°	832.0
22.5°	730.5
25°	647.2
27.5°	562.6
30°	458.3
32.5°	311.4
35°	175.7
37.5°	103.6
40°	69.3
42.5°	49.0
45°	34.3
47.5°	22.3
50°	14.0
52.5°	8.4
55°	6.3
57.5°	4.9
60°	3.5
62.5°	2.7
65°	2.2
67.5°	1.4
70°	1.4
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7



TEST NUMBER: P593485

CATALOG NUMBER: HC807D010-HM80520850-81NDH

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







85°		0.7
87.5°		0.7



(END OF REPORT)