

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583647

Luminaire Tested: **HC807D010-HM80520930-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520930-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 835.8 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583647

CATALOG NUMBER: HC807D010-HM80520930-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583647

CATALOG NUMBER: HC807D010-HM80520930-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	157299
5°	100895
10°	45578
15°	27503
20°	20956
25°	16924
30°	12402
35°	4491
40°	1675
45°	759
50°	240
55°	59
60°	37
65°	44
70°	0
75°	0
80°	107
85°	212



TEST NUMBER: P583647

CATALOG NUMBER: HC807D010-HM80520930-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	248.6	29.7
10°-20°	252.5	30.2
20°-30°	226.0	27.0
30°-40°	91.0	10.9
40°-50°	14.9	1.8
50°-60°	1.4	0.2
60°-70°	0.5	0.1
70°-80°	0.4	0.0
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.1	87.0
0°-40°	818.2	97.9
0°-60°	834.4	99.8
0°-90°	835.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	835.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5101	
5°	3260	249
15°	862	253
25°	497	226
35°	119	91
45°	17	15
55°	1	1
65°	1	1
75°	0	0
85°	1	1
90°	0	



TEST NUMBER: P583647

CATALOG NUMBER: HC807D010-HM80520930-81NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5101.1
0.5°	5085.3
1°	5019.5
1.5°	4913.7
2°	4753.4
2.5°	4563.7
3°	4326.3
3.5°	4065.7
4°	3808.1
4.5°	3519.4
5°	3259.5
5.5°	2976.5
6°	2746.9
6.5°	2507.7
7°	2319.9
7.5°	2121.2
8°	1961.5
8.5°	1801.1
9°	1680.6
9.5°	1547.9
10°	1455.6
12.5°	1073.6
15°	861.5
17.5°	736.0
20°	638.6
22.5°	560.9
25°	497.4
27.5°	433.8
30°	348.3
32.5°	223.9
35°	119.3
37.5°	65.8
40°	41.6
42.5°	27.6
45°	17.4
47.5°	10.6
50°	5.0
52.5°	1.7
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6



TEST NUMBER: P583647

CATALOG NUMBER: HC807D010-HM80520930-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		0.6
70°		0.0



(END OF REPORT)