

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593841

Luminaire Tested: **HC855D010-HM82555950-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC855D010-HM82555950-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5722.4 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593841

CATALOG NUMBER: HC855D010-HM82555950-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P593841

CATALOG NUMBER: HC855D010-HM82555950-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	261699
5°	238480
10°	203760
15°	177696
20°	158377
25°	140489
30°	115027
35°	66054
40°	29313
45°	17060
50°	9849
55°	5618
60°	3108
65°	1977
70°	1397
75°	917
80°	693
85°	1380



TEST NUMBER: P593841

CATALOG NUMBER: HC855D010-HM82555950-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	697.4	12.2
10°-20°	1564.6	27.3
20°-30°	1872.8	32.7
30°-40°	1133.0	19.8
40°-50°	317.5	5.5
50°-60°	98.6	1.7
60°-70°	28.1	0.5
70°-80°	7.6	0.1
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4134.8	72.3
0°-40°	5267.8	92.1
0°-60°	5684.0	99.3
0°-90°	5722.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5722.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8487	
5°	7704	697
15°	5566	1565
25°	4129	1873
35°	1755	1133
45°	391	318
55°	104	99
65°	27	28
75°	8	8
85°	4	3
90°	0	



TEST NUMBER: P593841

CATALOG NUMBER: HC855D010-HM82555950-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	8486.7
2.5°	8246.5
5°	7704.3
7.5°	7092.2
10°	6507.4
12.5°	5996.1
15°	5566.2
17.5°	5186.6
20°	4826.3
22.5°	4493.2
25°	4129.1
27.5°	3718.5
30°	3230.5
32.5°	2599.1
35°	1754.7
37.5°	1092.3
40°	728.2
42.5°	522.9
45°	391.2
47.5°	286.7
50°	205.3
52.5°	143.3
55°	104.5
57.5°	69.7
60°	50.4
62.5°	34.8
65°	27.1
67.5°	19.3
70°	15.5
72.5°	7.7
75°	7.7
77.5°	3.9
80°	3.9
82.5°	3.9
85°	3.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)