

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583654

Luminaire Tested: **HC807D010-HM80520930-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC807D010-HM80520930-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 945.4 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583654

CATALOG NUMBER: HC807D010-HM80520930-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P583654

CATALOG NUMBER: HC807D010-HM80520930-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 2 | 106 | 101 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 92 | 90 | 93 | 90 | 88 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 91 | 86 | 82 | 89 | 84 | 81 | 86 | 83 | 79 | 84 | 81 | 78 | 77 | 77 | 77 | 77 |
| 4 | 94 | 86 | 79 | 75 | 92 | 84 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 71 | 70 | 70 | 70 | 70 |
| 5 | 88 | 79 | 72 | 68 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 64 | 64 | 64 | 64 |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 60 | 59 | 59 | 59 | 59 |
| 7 | 78 | 68 | 61 | 57 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 60 | 56 | 63 | 59 | 55 | 54 | 54 | 54 | 54 |
| 8 | 74 | 63 | 57 | 52 | 73 | 63 | 56 | 52 | 62 | 56 | 52 | 60 | 55 | 51 | 59 | 55 | 51 | 50 | 50 | 50 | 50 |
| 9 | 70 | 59 | 53 | 48 | 69 | 59 | 52 | 48 | 58 | 52 | 48 | 57 | 51 | 48 | 56 | 51 | 47 | 46 | 46 | 46 | 46 |
| 10 | 66 | 55 | 49 | 45 | 65 | 55 | 49 | 45 | 54 | 48 | 44 | 53 | 48 | 44 | 52 | 48 | 44 | 43 | 43 | 43 | 43 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 22683 |
| 5° | 22073 |
| 10° | 21906 |
| 15° | 21578 |
| 20° | 20926 |
| 25° | 20146 |
| 30° | 18815 |
| 35° | 15573 |
| 40° | 9403 |
| 45° | 6332 |
| 50° | 4562 |
| 55° | 2602 |
| 60° | 1141 |
| 65° | 409 |
| 70° | 153 |
| 75° | 71 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P583654

CATALOG NUMBER: HC807D010-HM80520930-81WDC

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 67.7 | 7.2 |
| 10°-20° | 190.0 | 20.1 |
| 20°-30° | 271.0 | 28.7 |
| 30°-40° | 246.8 | 26.1 |
| 40°-50° | 116.4 | 12.3 |
| 50°-60° | 45.8 | 4.8 |
| 60°-70° | 7.3 | 0.8 |
| 70°-80° | 0.5 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 528.7 | 55.9 |
| 0°-40° | 775.4 | 82.0 |
| 0°-60° | 937.6 | 99.2 |
| 0°-90° | 945.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 945.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 736 | |
| 5° | 713 | 68 |
| 15° | 676 | 190 |
| 25° | 592 | 271 |
| 35° | 414 | 247 |
| 45° | 145 | 116 |
| 55° | 48 | 46 |
| 65° | 6 | 7 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P583654

CATALOG NUMBER: HC807D010-HM80520930-81WDC

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 735.6 |
| 2.5° | 726.1 |
| 5° | 713.1 |
| 7.5° | 705.8 |
| 10° | 699.6 |
| 12.5° | 689.4 |
| 15° | 675.9 |
| 17.5° | 659.0 |
| 20° | 637.7 |
| 22.5° | 615.2 |
| 25° | 592.1 |
| 27.5° | 563.9 |
| 30° | 528.4 |
| 32.5° | 480.6 |
| 35° | 413.7 |
| 37.5° | 319.7 |
| 40° | 233.6 |
| 42.5° | 179.5 |
| 45° | 145.2 |
| 47.5° | 119.3 |
| 50° | 95.1 |
| 52.5° | 71.5 |
| 55° | 48.4 |
| 57.5° | 30.4 |
| 60° | 18.5 |
| 62.5° | 11.2 |
| 65° | 5.6 |
| 67.5° | 2.9 |
| 70° | 1.7 |
| 72.5° | 0.6 |
| 75° | 0.6 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)